



### Basic features

<b>Application</b>	Pneumatic cylinder with integrated groove Used with BMF 303-HW-51 Holder suitable for 2 T slot dimension.
<b>Basic standard</b>	For slot dimensions see drawing Dimension tolerances: DIN ISO 2768 m
<b>Principle of operation</b>	BMF mounting bracket
<b>Scope of delivery</b>	Fastening part Mounting bracket
<b>Use</b>	for magnetic sensors BMF 305

### Material

<b>Material</b>	Aluminum
<b>Surface protection</b>	Anodized

### Mechanical data

<b>Mounting, holder</b>	Cylinder head screw ISO 1207 M3x14-A2
<b>Sensor attachment</b>	Cylinder head screw ISO 1207 M3x5-A2
<b>Size</b>	T-slot (SMC)
<b>Tightening torque</b>	1.5 Nm
<b>Tightening torque clamping screw</b>	0.5 Nm

### Environmental conditions

<b>Ambient temperature</b>	-40...85 °C
----------------------------	-------------

