



Basic features

Application	Pneumatic cylinder with integrated groove
Basic standard	Dimension tolerances: DIN ISO 2768 m
Principle of operation	BMF mounting bracket
Scope of delivery	Fastening screw Mounting bracket Offset screwdriver
Use	for magnetic sensors BMF 305

Environmental conditions

Ambient temperature	-40...85 °C
----------------------------	-------------

Material

Material	Aluminum
Surface protection	Anodized

Mechanical data

Mounting, holder	Threaded pin ISO 4027 M2x6-A2 Offset screwdriver ISO 2936 0.9
Sensor attachment	Knurled nut slotted screwdriver
Size	T-slot
Tightening torque	0.5 Nm
Tightening torque clamping screw	0.2 Nm

Help Views

