



Basic features

Application	Pneumatic cylinder with integrated mounting rail Bosch Type 0 822 350 / 351 / 352 / 353 / 354 / 355
Basic standard	Dimension tolerances: DIN ISO 2768 m
Principle of operation	BMF mounting bracket
Scope of delivery	Fastening part Mounting bracket
Use	for magnetic sensors BMF 32

Environmental conditions

Ambient temperature	-40...85 °C
----------------------------	-------------

Material

Material	Aluminum
Surface protection	anodized, black

Mechanical data

Mounting, holder	Cylinder head screw ISO 4762 M4x20-A2 Offset screwdriver ISO 2936 3.0
Sensor attachment	Threaded pin ISO 4026 M4x6-A2 offset screwdriver ISO 2936 2.0
Size	Dovetail (Bosch)
Tightening torque	0.5 Nm
Tightening torque clamping screw	1 Nm

Help Views

