

1) Emitter, 2) Receiver, 3) Optical axis



Basic features

Approval/Conformity	CE WEEE
Basic standard	IEC 60947-5-2
Principle of operation	Optical sensor head
Reference base unit	BAE SA-OH-029-...
Series	G02
Style	Cylinder Straight optics

Electrical connection

Cable diameter D	1.80 mm
Cable length L	1 m
Connection	Cable with connector, M8x1-Male, 1.00 m, PUR

Environmental conditions

Ambient temperature	-10...55 °C
Protection degree	IP65

Material

Housing material	Stainless steel
Material jacket	PUR
Material sensing surface	Epoxy

Remarks

For additional information, refer to user's guide.

Mechanical data

Dimension	$\varnothing 2 \times 12.6$ mm
Mounting	Diameter 2.0 mm

Optical features

Beam characteristic	Divergent
LED group per IEC 62471	Exempt Group
Light spot size	$\varnothing 0.4$ mm at 10 mm
Light type	LED, red light
Principle of optical operation	Through-beam sensor
Smallest part typ.	0.10 mm
Wave length	660 nm


Output/Interface

Switching output	for switching amplifier
------------------	-------------------------

Range/Distance

Range	0...200 mm
Rated operating distance S _n	200 mm

Connector Drawings



Opto Symbols

