

Basic features

Approval/Conformity	CE cULus EAC WEEE
Scope of delivery	Module Part label (21x) Port cover M8 (4x) Grounding strap Lock washer Short guide M4x6 screw
Style	Two-row

Display/Operation

IO-Link communication indicator	Green LED
Module supply indicator	Green LED
Sensor supply US indicator	Green LED
Switching function display	LED yellow

Electrical connection

Connection (COM 1)	M12x1-Male, 4-pin, A-coded
Connection slots	16x M8x1-Female, 3-pin
Contact, surface protection	nickel plated 2 µm/gold plated 0.4 µm

Electrical data

Burst	3A/4B
Configurable inputs/outputs	no
Current consumption without load, max.	90 mA
ESD	2A
IO-Link function	Device
IO-Link ports, number	1
Operating voltage U_b	18...30.2 VDC
Rated operating voltage U_e DC	24 V

Environmental conditions

Ambient temperature	-5...70 °C
Ambient temperature UL max.	45 °C
EN 60068-2-6, Vibration	5...61 Hz, constant amplitude 1 mm 61...500 Hz, constant acceleration 15 g
Protection degree	IP67 when threaded in
Storage temperature	-25...70 °C

Functional safety

MTTF (40 °C)	75.9 a
---------------------	--------

Material

Gasket, material	FKM 75
Housing material	Zinc, Die casting, nickel plated
Housing material, surface protection	nickel plated
Housing shield	yes
Surface protection	Cu 15 µm Ni 15 µm

Mechanical data

Dimension	30 x 32.8 x 220 mm
Mounting	2-hole screw mount
Mounting ground strap	M4 internal thread

Output/Interface


Cycle time min.	3.5 ms
Digital inputs	16x PNP, Type 3
Extension port	yes
IO-Link version	1.1
Interface	IO-Link 1.1
Process data IN	2 bytes
Process data cycle min.	3.5 ms
Transfer rate	COM2 (38.4 kBaud)

Remarks

See short guide

For more information about MTTF and B10d see MTTF / B10d Certificate

Indication of the MTTF- / B10d value does not represent a binding composition and/or life expectancy assurance; these are simply experiential values with no warranty implications. These declared values also do not extend the expiration period for defect claims or affect it in any way.

Connector Drawings


IO-Link

PIN 1: +24V

PIN 2: n.c.

PIN 3: GND, reference potential

PIN 4: IO-Link



Input Ports

PIN 1: +24V, 0.2A

PIN 3: 0V

PIN 4: Input