

1) Optical axis receiver, 2) Optical axis emitter



Basic features

Approval/Conformity	CE cULus Ecolab FDA compliant EAC WEEE
Basic standard	IEC 60947-5-2
Principle of operation	Photoelectric sensor
Series	18E
Style	Cylinder Straight optics

Electrical data

Load capacitance max. at Ue	0.1 µF
No-load current I _o max. at Ue	40 mA
Operating voltage U _b	10...30 VDC
Rated insulation voltage U _i	75 V DC
Rated operating current I _e	100 mA
Rated operating voltage U _e DC	24 V
Ripple max. (% of U _e)	15 %
Switching frequency	400 Hz
Turn-off delay t _{off} max.	1.25 ms
Turn-on delay t _{on} max.	1.25 ms
Utilization category	DC -13
Voltage drop U _d max. at I _e	2.5 V

Display/Operation

Adjuster	no
----------	----

Electrical connection

Connection	Connector, M12x1-Male, 4-pin
Contact, surface protection	Gold plated
Polarity reversal protected	yes
Protection against device mix-ups	yes
Short-circuit protection	yes

Environmental conditions

Ambient temperature	-25...70 °C
Contamination scale	3
EN 60068-2-27, Shock	Half-sinus, 30 gn, 11 ms, 3x6 Half-sinus, 100 gn, 2 ms, 3x8000
EN 60068-2-6, Vibration	10...55 Hz, amplitude 1 mm, 3x30 min 10...2000 Hz, amplitude 1 mm, 30 gn, 3x5 h
IP rating per DIN 40050	IPx9K
Protection degree	IP68/IP67

Functional safety

MTTF (40 °C)	537 a
--------------	-------

Photoelectric Sensors
BOS 18E-PA-RD20-S4
 Order Code: BOS01KE



Material

Housing material	Stainless steel (1.4404)
Material sensing surface	Glass

Mechanical data

Dimension	Ø 18 x 75 mm
Mounting	Nut M18x1
Tightening torque max.	40 Nm

Optical features

Ambient light max.	10000 Lux
Beam characteristic	Divergent
LED group per IEC 62471	Exempt Group
Light spot size	Ø 50 mm at 600 mm
Light type	LED, red light
Principle of optical operation	Diffuse sensor, energetic
Switching function, optical	Light/dark switching
Wave length	640 nm

Output/Interface

Switching output	PNP normally open (NO)
	PNP NC Pins 4-2

Range/Distance

Hysteresis H max. (% of Sr)	10.0 %
Range	500 mm
Rated operating distance Sn	500 mm
Temperature drift max. (% of Sr)	10 %

Remarks


Order accessories separately.
 For additional information, refer to user's guide.
 The sensor is functional again after the overload has been eliminated.
 Reference object (target): gray card, 200 x 200, 90 % remission, axial approach.
 For more information about MTTF and B10d see MTTF / B10d Certificate

Indication of the MTTF- / B10d value does not represent a binding composition and/or life expectancy assurance; these are simply experiential values with no warranty implications. These declared values also do not extend the expiration period for defect claims or affect it in any way.

Connector Drawings



Wiring Diagrams



Opto Symbols

