


1) Optical axis, 2) Output function



Basic features

Approval/Conformity	CE cULus EAC WEEE
Basic standard	IEC 60947-5-2
Principle of operation	Photoelectric sensor
Reference reflector	BOS R-1
Series	18KF
Style	Flat cylinder Straight optics
Trademark	Global

Electrical data

No-load current I_0 max. at U_e	35 mA
Operating voltage U_b	10...30 VDC
Rated insulation voltage U_i	75 V DC
Rated operating current I_e	100 mA
Rated operating voltage U_e DC	24 V
Ripple max. (% of U_e)	8 %
Switching frequency	1000 Hz
Turn-off delay t_{off} max.	0.5 ms
Turn-on delay t_{on} max.	0.5 ms
Voltage drop U_d max. at I_e	2 V

Display/Operation

Display	Output function- LED yellow
---------	-----------------------------

Electrical connection

Connection	Connector, M12x1-Male, 4-pin
Polarity reversal protected	yes
Short-circuit protection	yes

Environmental conditions

Ambient temperature	-25...55 °C
EN 60068-2-27, Shock	Half-sinus, 30 gn, 11 ms, 3x6
EN 60068-2-6, Vibration	10...55 Hz, amplitude 0.5 mm, 3x30 min
Protection degree	IP67

Functional safety

MTTF (40 °C) 834 a

Material

Housing material PBT
 Material sensing surface PMMA

Mechanical data

Dimension Ø 18 x 71.5 mm
 Mounting Nut M18x1
 Screw M3
 Tightening torque max. 1.5 Nm

Optical features

Ambient light max. 5000 Lux
 Blind zone 100 mm
 Light type LED infrared
 Polarizing filter no
 Principle of optical operation Retroreflective sensor
 Switching function, optical dark-on
 Wave length 880 nm

Output/Interface

Switching output NPN normally open (NO)
 NPN NC Pins 4-2

Range/Distance

Range 0...5 m
 Rated operating distance Sn 5 m Adjustable

Remarks

The sensor is functional again after the overload has been eliminated.

For additional information, refer to user's guide.

Order accessories separately.

Actuation object (target): gray card, 200 x 200, 90 % remission, lateral approach, approach direction vertical to lens axis plane.


For more information about MTTF and B10d see MTTF / B10d Certificate

Indication of the MTTF- / B10d value does not represent a binding composition and/or life expectancy assurance; these are simply experiential values with no warranty implications. These declared values also do not extend the expiration period for defect claims or affect it in any way.

Connector Drawings



Wiring Diagrams



Opto Symbols

