

1) Output function/Error, 2) Operating voltage, 3) Sn, 4) Bar display for switching distance, 5) Optical axis receiver, 6) Optical axis emitter, 7) rotatable 270°



IND. CONT. EQ
 77HA
 for use in the secondary of
 a class 2 source of supply



Basic features

Approval/Conformity	Ecolab CE cULus EAC WEEE
Basic standard	IEC 60947-5-2
Principle of operation	Photoelectric sensor
Series	23K
Style	Square Connection can be rotated

Electrical data

Border range energetic	1200 mm
Input function	Light-on/dark-on
No-load current I_0 max. at U_e	30 mA
Operating voltage U_b	10...30 VDC
Protection class	II
Rated insulation voltage U_i	75 V DC
Rated operating current I_e	100 mA
Rated operating voltage U_e DC	24 V
Ready delay t_v max.	300 ms
Residual current I_r max.	50 μ A
Ripple max. (% of U_e)	10 %
Switching frequency	600 Hz
Turn-off delay t_{off} max.	0.83 ms
Turn-on delay t_{on} max.	0.83 ms
Utilization category	DC -13
Voltage drop U_d max. at I_e	2 V

Display/Operation

Adjuster	Adjusting screw
Display	Output function- LED yellow LED green: Power Error - LED yellow, flashing Switching distance - bar display
Setting	Rated switching distance (Sn)

Electrical connection

Connection	Connector, M12x1-Male, 4-pin
Polarity reversal protected	yes
Protection against device mix-ups	yes
Short-circuit protection	yes

Environmental conditions

Ambient temperature	-20...60 °C
EN 60068-2-27, Shock	Half-sinus, 30 gn, 11 ms, 3x6
EN 60068-2-6, Vibration	10...55 Hz, amplitude 0.5 mm, 3x30 min
IP rating per DIN 40050	IPx9K
Protection degree	IP6x

Functional safety

MTTF (40 °C)	466 a
---------------------	-------

Material

Housing material	PC ABS
Material sensing surface	PMMA

Mechanical data

Dimension	23 x 51 x 52.4 mm
Mounting	Screw M4
Tightening torque max.	1.5 Nm

Optical features

Ambient light max.	5000 Lux
Beam characteristic	Focus, typical at 500 mm
LED group per IEC 62471	Exempt Group
Light spot size	15 x 15 mm at focal point
Light type	LED, red light
Principle of optical operation	Diffuse sensor, triangulation
Special optical feature	Background suppression
Switching function, optical	Light/dark switching
Wave length	640 nm

Output/Interface

Switching output	NPN normally open/normally closed (NO/NC)
-------------------------	---

Range/Distance

Distance deviation 18 % max. (% of Sr)	15 %
Hysteresis H max. (% of Sr)	4.0 %
Range	3...800 mm
Rated operating distance Sn	800 mm Adjustable

Remarks


The sensor is functional again after the overload has been eliminated.
 Reference object (target): gray card, 200 x 200, 90 % remission, axial approach.
 For additional information, refer to user's guide.
 Order accessories separately.
 For more information about MTTF and B10d see MTTF / B10d Certificate

Indication of the MTTF- / B10d value does not represent a binding composition and/or life expectancy assurance; these are simply experiential values with no warranty implications. These declared values also do not extend the expiration period for defect claims or affect it in any way.

Connector Drawings



Wiring Diagrams



Opto Symbols

