

1) Optical axis emitter, 2) Optical axis receiver, 3) Output function



### Basic features

Approval/Conformity	cULus CE EAC WEEE
Basic standard	IEC 60947-5-2
Principle of operation	Photoelectric sensor
Series	Q08M
Style	Square Connection 90°

### Display/Operation

Display	Limit range - LED yellow, flashing LED yellow: Light received
---------	--

### Electrical connection

Cable diameter D	3.00 mm
Cable length L	0.2 m
Connection	Cable with connector, 0.20 m, PUR
Contact, surface protection	Gold plated
Polarity reversal protected	yes
Protection against device mix-ups	yes
Short-circuit protection	yes

### Electrical data

Load capacitance max. at Ue	0.5 µF
No-load current I <sub>o</sub> max. at Ue	15 mA
Operating voltage U <sub>b</sub>	10...30 VDC
Rated insulation voltage U <sub>i</sub>	75 V DC
Rated operating current I <sub>e</sub>	100 mA
Rated operating voltage U <sub>e</sub> DC	24 V
Ready delay t <sub>v</sub> max.	20 ms
Ripple max. (% of U <sub>e</sub> )	10 %
Switching frequency	500 Hz
Turn-off delay t <sub>off</sub> max.	1 ms
Turn-on delay t <sub>on</sub> max.	1 ms
Utilization category	DC -13
Voltage drop U <sub>d</sub> max. at I <sub>e</sub>	0.7 V

### Environmental conditions

Ambient temperature	-5...55 °C
EN 60068-2-27, Shock	Half-sinus, 100 gn, 2 ms, 3x8000 Half-sinus, 30 gn, 11 ms, 3x6
EN 60068-2-6, Vibration	10...2000 Hz, amplitude 1 mm, 30 gn, 3x5 h 10...55 Hz, amplitude 1 mm, 3x30 min
Protection degree	IP67

**Material**

Housing material	Zinc, Die casting, nickel plated
Material jacket	PUR
Material sensing surface	PMMA
Surface protection	nickel plated

**Mechanical data**

Dimension	8 x 44 x 8 mm
Mounting	Screw M3

**Optical features**

Beam characteristic	Divergent
LED group per IEC 62471	Exempt Group
Light spot size	Ø 3.0 mm Light exit
Light type	LED, red light
Principle of optical operation	Diffuse sensor, energetic
Switching function, optical	Light-on
Wave length	645 nm

**Output/Interface**

Switching output	PNP normally open (NO)
------------------	------------------------

**Range/Distance**

Range	1...60 mm
Rated operating distance Sn	60 mm

**Remarks**

Order accessories separately.

For additional information, refer to user's guide.

Only for applications per NFPA 79 (machines with a supply voltage of maximum 600 V). Use an R/C (CYJV2) cable with suitable properties for attaching the device.


Actuation object (target): gray card, 200 x 200, 90 % remission, lateral approach, approach direction vertical to lens axis plane.

The sensor is functional again after the overload has been eliminated.

**Connector Drawings**



**Wiring Diagrams**



**Opto Symbols**

