



1) Reference edge, 2) Sensing surface, 3) Function indicator FD/FE/LL



### Basic features

Approval/Conformity	CE WEEE
Basic standard	IEC 60947-5-2
Operating principle	1-4. Switch position: Inductive
Version	Inductive

### Display/Operation

Function indicator	1-4. Switch position: Optical fiber
--------------------	-------------------------------------

### Electrical connection

Connection type	1-4. Switch position: Screw terminal
Electrical version	3-/4-wire

### Electrical data

Continuous current	1-4. Switch position: 0.2 A
Rated operating voltage Ue	1-4. Switch position: 24 V DC

### Environmental conditions

Ambient temperature	-25...70 °C
Protection degree	IP67

### Functional safety

MTTF (40 °C)	BES 517-110: 490 a
--------------	--------------------

### Material

Housing material	Aluminum, Anodized
Housing material, surface protection	Anodized

### Mechanical data

Dimension	79 x 60 x 77.5 mm
Distance cam - active surface	1-4. Switch position: 0...1.62 mm
Flange, feed-through	None
Installation	Vertical
Plunger spacing 1st switch position	12 mm
Switching element	1-4. Switch position: BES 517-110

### Output/Interface

Switching output	PNP complementary
------------------	-------------------

### Range/Distance

Assured operating distance Sa	1-4. Switch position: 1.6 mm
Range	2 mm
Rated operating distance Sn	1-4. Switch position: 2.0 mm
Switch position spacing	12 mm

## Wiring Diagrams

