



1) Reference edge



Basic features

Approval/Conformity	CE CCC WEEE
Basic standard	IEC 60947-5-2
DIN switch	DIN 43693
Operating principle	1. Switch position: Mechanical
Version	Snap contact

Display/Operation

Function indicator	1. Switch position: None
---------------------------	--------------------------

Electrical connection

Connection type	1. Switch position: Screw terminal
------------------------	------------------------------------

Electrical data

Continuous current	1. Switch position: 6 A
Rated operating voltage Ue	1. Switch position: 250 V AC
Switching function mechanical	Double-interrupting galvanically isolated One NO and one NC Dual changeover
Switching rate	1. Switch position: 300/min

Environmental conditions

Ambient temperature	-5...85 °C
Protection degree	IP67

Functional safety

B10d (EN ISO 13849-1)	BSE 30.0: 30 mil. Switching operations
------------------------------	--

Material

Housing material	Aluminum, Anodized
Housing material, surface protection	Anodized
Material contacts	1. Switch position: Silver, gold plated
Plunger material	1. Switch position: Stainless steel (1.4034)

Mechanical data

Approach direction	lateral or at right angles to mounting surface
Approach speed	1. Switch position: 120 m/min
Dimension	74 x 28 x 61 mm
Distance cam - reference edge	1. Switch position: 4.50...5.00 mm
Flange, feed-through	None
Installation	any
Life expectancy mechanical	1. Switch position: 30 million Switching operations
Number of switching positions	1x Roller bearing
Plunger spacing 1st switch position	14 mm
Plunger style	1st switch position: Roller bearing
Switch actuation force	1. Switch position: 20 N
Switching element	1. Switch position: BSE 30.0

Range/Distance

Reproducibility

1. Switch position: ± 0.01 mm

Wiring Diagrams

BSE 30.0

