


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION

© COPYRIGHT BY

| REVISIONS |   |      |     |                           | DATE   | APPROVED  |
|-----------|---|------|-----|---------------------------|--------|-----------|
| P         | F | ZONE | LTR | DESCRIPTION               |        |           |
| D         |   | D3   |     | REVISED PER ECO-11-005033 | 2APR11 | RK<br>HMR |

WHITE WITH GREEN CENTER  
 WHITE WITH ORANGE CENTER  
 BLUE WITH WHITE CENTER  
 WHITE WITH BLUE CENTER  
 ORANGE WITH WHITE CENTER  
 GREEN WITH WHITE CENTER

STUFFER CAP LABEL  
 HAVING CLEAR BACKGROUND





1. BARREL TERMINALS WILL ACCEPT ONE OR TWO WIRES OF THE SAME SIZE PER TERMINAL. MAX WIRE SIZE IS 22 AWG WITH .060 DIAMETER INSULATION. MIN WIRE SIZE IS 26 AWG WITH .037 DIAMETER INSULATION.

2. STUFFER CAP SHIPPED NOT ASSEMBLED.



3. MATERIALS: STUFFER CAP-POLYCARBONATE (NATURAL)  
 BARREL TERMINAL-TIN COATED PHOSPHOR BRONZE  
 LABEL ADHESIVE BACKED POLYESTER  
 CONTACTS-NICKEL PLATED HIGH STRENGTH COPPER ALLOY HAVING SELECTIVE GOLD PLATING IN CONTACT AREA AND SELECTIVE TIN PLATING IN BARREL TERMINAL AREA.  
 HOUSING & KEYSTONE-THERMOPLASTIC (BLACK) 94V-0 RATED

4. MOUNTING PANEL THICKNESS-.062 NOMINAL

1. 125 DIAMETER  
 AMP BARREL TERMINAL  
 G REQUIRED



WIRING DIAGRAM

BACK PANEL  
SCALE 2:1FRONT PANEL  
SCALE 2:1

553983-1 AS SHOWN

|                                                                                                       |  |                                                                                                      |  |                                                  |                  |
|-------------------------------------------------------------------------------------------------------|--|------------------------------------------------------------------------------------------------------|--|--------------------------------------------------|------------------|
| UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES.<br>TOLERANCES ON:<br>DECIMALS ± .010<br>ANGLES = |  | CONTRACT NO<br>DR S. Pozabanchuk 3-29-84<br>CHK Stephen Doss 6-5-84<br>APPD Gene Reed 6-5-84<br>APPD |  | PART NO                                          |                  |
| MATERIAL<br>3                                                                                         |  | DSGN APPD                                                                                            |  | NAME<br>KEYSTONE JACK KIT,<br>6 POSITION, MARKED |                  |
| FINISH<br>3                                                                                           |  | OTHER APPD                                                                                           |  | SIZE<br>C                                        | FSCM NO<br>00779 |
|                                                                                                       |  |                                                                                                      |  | DRAWING NO<br>553983                             | REV<br>D3        |
|                                                                                                       |  |                                                                                                      |  | SCALE 4:1                                        | SHEET 1 OF 1     |

CUSTOMER DRAWING

553983