


1) Optical axis receiver, 2) Optical axis emitter, 3) Operating voltage/Error, 4) Light reception/limit area



Basic features

Approval/Conformity	CE cULus EAC WEEE
Basic standard	IND. CONT. EQ. 81U2 Class 2 Type 1
Principle of operation	IEC 60947-5-2 Photoelectric sensor
Series	12M
Style	Cylinder Straight optics

Display/Operation

Adjuster	no
Display	LED green: Power Error - LED green, flashing Limit range - LED yellow, flashing LED yellow: Light received

Electrical connection

Connection	Connector, M12x1-Male, 4-pin
Contact, surface protection	Gold plated
Polarity reversal protected	yes
Short-circuit protection	yes

Electrical data

Load capacitance max. at U_e	0.2 μ F
No-load current I_o max. at U_e	20 mA
Operating voltage U_b	10...30 VDC
Rated operating current I_e	100 mA
Rated operating voltage U_e DC	24 V
Ripple max. (% of U_e)	15 %
Switching frequency	1000 Hz
Turn-off delay t_{off} max.	0.5 ms
Turn-on delay t_{on} max.	0.5 ms
Utilization category	DC -13
Voltage drop U_d max. at I_e	1.5 V

Environmental conditions

Ambient temperature	-5...60 °C
Contamination scale	3
EN 60068-2-27, Shock	Half-sinus, 30 gn, 11 ms, 3x6 Half-sinus, 100 gn, 2 ms, 3x8000
EN 60068-2-6, Vibration	10...55 Hz, amplitude 1 mm, 3x30 min 10...2000 Hz, amplitude 1 mm, 30 gn, 3x5 h
Protection degree	IP67

Functional safety

MTTF (40 °C)	1561 a
--------------	--------

Photoelectric Sensors
BOS 12M-NA-RF10-S4
Order Code: BOS01UP

BALLUFF

Material

Housing material	Brass, nickel plated
Material sensing surface	PMMA
Surface protection	nickel plated

Mechanical data

Dimension	Ø 12 x 60 mm
Distance deviation 6 % max. (% of Sr)	5.0 %
Mounting	Nut M12x1
Tightening torque max.	7 Nm 15 Nm

Optical features

Ambient light max.	50000 Lux
Beam characteristic	Focus, typical at 25 mm
LED group per IEC 62471	Exempt Group
Light spot size	Ø 2 mm at 25 mm
Light type	Red light
Principle of optical operation	Diffuse sensor, triangulation
Smallest part typ.	Ø 0.05 mm wire
Special optical feature	Fixed focus Fixed background suppression
Switching function, optical	Light-on dark-on
Wave length	650 nm

Output/Interface

Switching output	NPN normally open (NO) NPN NC Pins 4-2
------------------	---

Range/Distance

Distance deviation 18 % max. (% of Sr)	1 %
Hysteresis H max. (% of Sr)	1.0 %
Range	1...25 mm
Rated operating distance Sn	25 mm
Repeat accuracy max. (% of Sr)	1.0 %
Temperature drift max. (% of Sr)	5 %

Remarks

Order accessories separately.

For additional information, refer to user's guide.

Only for applications per NFPA 79 (machines with a supply voltage of maximum 600 V). Use an R/C (CYJV2) cable with suitable properties for attaching the device.

Reference object (target): gray card, 100 x 100, 90 % remission, axial approach.

The sensor is functional again after the overload has been eliminated.


For more information about MTTF and B10d see MTTF / B10d Certificate

Indication of the MTTF- / B10d value does not represent a binding composition and/or life expectancy assurance; these are simply experiential values with no warranty implications. These declared values also do not extend the expiration period for defect claims or affect it in any way.

Connector Drawings



Wiring Diagrams



Opto Symbols

