







参照基板レイアウト(マウント面)


P.W.BOARD PATTERN

DIM.(REF)


推奨メタルマスク厚さ : 0.1mm

RECOMMENDED METAL MASK THICKNESS : 0.1mm

推奨開口率 : 80%
APERTURE RATE : 80%




FPC構成推奨仕様
STRUCTURE OF FPC




FPCについて (ABOUT FPC)
抜き方向は、導体側から補強版側を推奨致します。
補強板材質はポリイミド、接着剤は熱硬化接着剤を推奨します。
尚、接着剤の接点部への付着は導通不良の原因になりますので、染み出しが無い様、お願い致します。
RECOMMENDED PUNCHER DIRECTION:
FROM CONDUCTOR SIDE TO STIFFENER BOARD SIDE.
RECOMMENDED MATERIAL:
STIFFENER BOARD: POLYIMIDE
BONDING AGENT: THERMOSETTING AGENT
PLEASE PUT APPROPRIATE AMOUNT OF ADHESIVE ON ADHEREND
BECAUSE THERE IS A POSSIBILITY THAT
THE EXTRA ADHESIVE CAUSES THE DEFECT IN ELECTRICAL CONTINUITY.

※1 補強板の長さが図面通りに確保できない場合は、カバーレイと補強板のオーバーラップ寸法を0.5mm以上としてください。
WHEN STIFFNER BOARD DIMENSION CAN NOT SECURE AS DRAWING, PLEASE GIVE THE OVERLAP SIZE OF COVER FILM AND STIFFNER BOARD AS 0.5mm MINIMUM.



NOTES

- 1. 製品詳細寸法については、図面 5047401000をご参照下さい。
REFER TO THE 5047401000 ABOUT DIMENSIONS IN DETAIL.
- 2. 梱包数量 : 5000 個/リール
NUMBER OF CONNECTORS : 5000 PCS/REEL
- 3. リードテープ長さ
LEAD TAPE LENGTH



- 4. トップテープの剥離強度については、IEC60286-3 に準拠
TOP TAPE PEEL FORCE IS DEFINED BY IEC60286-3.
- 5. 材料
キャリアテープ : ポリスチレン (PS)
トップテープ : PET, OTHER
リール : ポリスチレン (PS) <リサイクル材を含む>

MATERIAL
CARRIER TAPE : POLYSTYRENE(PS)
TOP TAPE : PET, OTHER
REEL ; POLYSTYRENE(PS)
<RECYCLE MATERIAL CONTAINED>

32	37.4	33.4	504740-6100	61
			504740-5100	51
24	29.4	25.4	504740-4500	45
			504740-4100	41
			504740-3900	39
			504740-3700	37
			504740-3300	33
			504740-2500	25
16	21.4	17.4	504740-2300	23
			504740-1900	19
			504740-1100	11
テープ幅 TAPE WIDTH	B	A	EMBOSSSED PACKAGE	CIRCUIT
			オーダー番号 ORDER NO.	
CONNECTOR SERIES NO.			504740-**09	

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION													
DIMENSION UNITS		SCALE		CURRENT REV DESC:									
mm		1:1											
GENERAL TOLERANCES (UNLESS SPECIFIED)				molex 0.3 FPC CONN. BACK FLIP HGT=0.95MM EMBSTP PKG PRODUCT CUSTOMER DRAWING									
ANGULAR TOL ± 1.0 °													
4 PLACES		± 0.2								EC NO: 692510		2022/01/17	
3 PLACES		± 0.25								DRWN: NARENC		2022/01/19	
2 PLACES		± 0.3								CHK'D: TKON		2022/01/20	
1 PLACE		± 0.1								APPR: SHOSHIKAWA			
INITIAL REVISION:													
0 PLACES		±		DRWN: TONO		2013/12/03		DOCUMENT NUMBER					
APPR: YNOGAWA				2014/03/05		SD-504740-002		DOC TYPE					
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		DOC PART					
						A3-SIZE		001					
				SERIES		MATERIAL NUMBER		REVISION					
				504740		SEE TABLE		C					
						CUSTOMER		SHEET NUMBER					
						GENERAL MARKET		1 OF 1					

DOCUMENT STATUS	P1	RELEASE DATE	2022/01/20	04:08:20
-----------------	----	--------------	------------	----------