




.018 THICK  
(.45)  
TRANSISTOR LEADS  
REF



2759 TERMINAL SHOWN FOR REF ONLY



NOTES:

1. MATERIAL: GLASS FILLED POLYESTER, UL94V-0, COLOR: NATURAL.
2. FINISH: N/A
3. PRODUCT SPECIFICATION: NONE.
4. PACKAGING: BULK.
5. FOR USE WITH TERMINAL NO. 2759.
6. DIMENSIONS GIVEN ACROSS CENTERLINES ARE SYMMETRICAL ABOUT THOSE CENTERLINES WITHIN HALF THE TOTAL TOLERANCE.

UPDATE PER ECN ECN NO: UCP2006-0888 2005/10/19 T1 DRW:ADERR CHKD:SSOUSEK APPR:FSM TH 2005/10/20 2005/10/21	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE ---	DESIGN UNITS INCH	THIRD ANGLE PROJECTION	
		mm	INCH	DRAWN BY SAMI EC	DATE 1992/04/29	TITLE TRANSISTOR SOCKET 3 CKT FOR CRIMP TERMINALS, .100 CENTERS			
		4 PLACES ± --- ± ---	3 PLACES ± --- ± .010	CHECKED BY PA TEL	DATE 1992/04/29	MOLEX INCORPORATED MATERIAL NO. 10-17-2032 DOCUMENT NO. SD-4025 SHEET NO. 1 OF 1			
		2 PLACES ± 0.25 ± .014	1 PLACE ± 0.36 ± ---	APPROVED BY LENZ	DATE 1992/04/29				
ANGULAR ±1/2°		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE C		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			