SD-39850-002

NO. OF CIRC. "XX"	DIM. "A"	DIM. "B"	MATERIAL NO. (STANDARD)	MATERIAL NO. (-10A OPTION)	MATERIAL NO. (-72 OPTION)	MATERIAL NO. (-10A-72 OPT.)
02	10.2 [.40]	5.00 [.197]	398500102	398500302		
03	15.2 [.60]	10.00 [.394]	398500103	398500303		
04	20.2 [.80]	15.00 [.591]	398500104	398500304		
05	25.2 [.99]	20.00 [.787]	398500105	398500305		
06	30.2 [1.19]	25.00 [.984]	398500106	398500306		
07	35.2 [1.39]	30.00 [1.181]	398500107	398500307		
08	40.2 [1.58]	35.00 [1.378]	398500108	398500308		
09	45.2 [1.78]	40.00 [1.575]	398500109	398500309		
10	50.2 [1.98]	45.00 [1.772]	398500110	398500310		
11	55.2 [2.17]	50.00 [1.969]	398500111	398500311		
12	60.2 [2.37]	55.00 [2.165]	398500112	398500312		
13	65.2 [2.57]	60.00 [2.362]	398500113	398500313		
14	70.2 [2.76]	65.00 [2.559]	398500114	398500314		
15	75.2 [2.96]	70.00 [2.756]	398500115	398500315		
16	80.2 [3.16]	75.00 [2.953]	398500116	398500316		
17	85.2 [3.35]	80.00 [3.150]	398500117	398500317		
18	90.2 [3.55]	85.00 [3.346]	398500118	398500318		
19	95.2 [3.75]	90.00 [3.543]	398500119	398500319		
20	100.2 [3.95]	95.00 [3.740]	398500120	398500320		
21	105.2 [4.14]	100.00 [3.937]	398500121	398500321		
22	110.2 [4.34]	105.00 [4.134]	398500122	398500322		
23	115.2 [4.54]	110.00 [4.331]	398500123	398500323		
24	120.2 [4.73]	115.00 [4.528]	398500124	398500324		





5 CIRCUIT SHOWN



VIEW Z-Z



NOTES:

1. MATERIAL: SEE TABLE
2. FINISHES: SEE TABLE
3. PRODUCT SPECIFICATION: NOT REQUIRED
4. PACKAGING: NOT REQUIRED
5. MATES WITH: NONE
6. "XX" REFERS TO THE QUANTITY OF CIRCUITS.
7. ASSEMBLY WITH -72 OPTION DOES NOT HAVE WIRE PROTECTORS.

ITEM	QTY.	DESCRIPTION	MATERIAL	FINISH
4	XX	SCREW, M2.5 X 0.45 CPT SLOTTED	STEEL	ZN, CLEAR CHROMATE
3	XX	WIRE PROTECTOR	PHOS. BRONZE	TIN PLATE
2	XX	TERMINAL, PC, 45°	BRASS	TIN PLATE
1	1	INSULATOR, SINGLE ROW	THERMOPLASTIC	BLACK

EC NO. RELEASED
DRWN: CLY
CH'K:
APPR:
DESCRIPTION
A
REV

QUALITY SYMBOLS
MAJOR:
CRITICAL: C
SPC: S

GENERAL TOLERANCES: (UNLESS SPECIFIED)

	mm	INCH
4 PLACES		±.0015
3 PLACES	±.038	±.005
2 PLACES	±.13	±.01
1 PLACE	±.3	
ANGULAR:	±2°	

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

SCALE 3:1
DESIGN UNITS ☐ mm ☒ INCH
THIRD ANGLE PROJECTION
DRAWN BY & DATE C. YORK 12-06-04
CHECKED BY & DATE
APPROVED BY & DATE
CAD FILENAME 854XX
MATERIAL NO. SEE CHART
DRAWING NO. SD-39850-002
SHEET NO. 1 OF 1
SIZE B

PROJECT NO. -
DIMENSIONS: ☒ mm/INCH ☐ INCH/mm ☐ mm ONLY
SHT -
REV -
REVISE ON CAD ONLY

TITLE: SR BTS, CS, 5MM [.197"], 45° ASSY

MOLEX INCORPORATED

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.