

1) Optical axis, 2) Sn, 3) Output function, 4) stability



IND. CONT. EQ
 1TD4
 for use in the secondary of
 a class 2 source of supply



Basic features

Approval/Conformity	CE cULus EAC WEEE
Basic standard	IEC 60947-5-2
Principle of operation	Photoelectric sensor
Reference reflector	BOS R-1
Series	18M
Style	Cylinder Straight optics

Electrical data

No-load current I_0 max. at U_e	35 mA
Operating voltage U_b	10...30 VDC
Protection class	II
Rated insulation voltage U_i	75 V DC
Rated operating current I_e	100 mA
Rated operating voltage U_e DC	24 V
Ripple max. (% of U_e)	8 %
Switching frequency	1500 Hz
Turn-off delay t_{off} max.	0.33 ms
Turn-on delay t_{on} max.	0.33 ms
Voltage drop U_d max. at I_e	2 V

Display/Operation

Adjuster	Potentiometer 270°
Display	Output function- LED yellow LED green: Power
Setting	Sensitivity (S_n)

Environmental conditions

Ambient temperature	-10...50 °C
EN 60068-2-27, Shock	Half-sinus, 50 gn, 500 ms, 3x3
EN 60068-2-6, Vibration	10...55 Hz, amplitude 0.5 mm, 3x30 min
Protection degree	IP67

Electrical connection

Connection	Connector, M12x1-Male, 4-pin
Polarity reversal protected	yes
Short-circuit protection	yes

Functional safety

MTTF (40 °C)	739 a
--------------	-------

Material

Housing material	Brass, nickel plated
Material sensing surface	PMMA
Surface protection	nickel plated

Mechanical data

Dimension	Ø 18 x 81.5 mm
Mounting	Nut M18x1
Tightening torque max.	22 Nm

Optical features

Ambient light max.	3000 Lux
Average power Po max.	390 µW
Blind zone	100 mm
Laser class per IEC 60825-1	1
Light type	Laser red light
Polarizing filter	yes
Principle of optical operation	Retroreflective sensor
Pulse duration t max.	6.0 µs
Pulse frequency	25 kHz
Switching function, optical	dark-on
Wave length	650 nm

Output/Interface

Switching output	PNP normally open (NO) PNP NC Pins 2-4
------------------	---

Range/Distance

Range	0...16 m
Rated operating distance Sn	16 m Adjustable

Remarks

Actuation object (target): gray card, 200 x 200, 90 % remission, lateral approach, approach direction vertical to lens axis plane.

Polarizing filters prevent spurious switching due to reflecting and shiny parts.

For additional information, refer to user's guide.

Order accessories separately.


For more information about MTTF and B10d see MTTF / B10d Certificate

Indication of the MTTF- / B10d value does not represent a binding composition and/or life expectancy assurance; these are simply experiential values with no warranty implications. These declared values also do not extend the expiration period for defect claims or affect it in any way.

Connector Drawings




Wiring Diagrams



Opto Symbols



Warning Symbols



LASER CLASS 1 per IEC 60825-1