

NAME: H+ DATE: 10.1.79

THIS INFORMATION IS CONFIDENTIAL AND IS DISCLOSED TO YOU ON CONDITION THAT NO FURTHER DISCLOSURE IS MADE BY YOU TO OTHER THAN TE PERSONNEL WITHOUT WRITTEN AUTHORIZATION FROM TE INCORPORATED, HARRISBURG, PA.

WAS 78-9833

NOTE

- 1 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- 2 OBSOLETE

DRAWING VALID FROM
ZEICHNUNG GÜLTIG AB

[illegible]

✓	H	REV. PER ECN 8809	Q.40	15.1.83
		WIN NO. 8-327 360-2		
		1-926 409-3		
		PHN NO. 8-327 360-3	2.14	22.9.88
		WAS 1-926 409-2		
G		REV DDA F/N 9647	Reg. No.	0102877
E		REV. PER ECN 8539	1112.85	
D		REV. PER ECN 8197	5.7.83	
C		REV. PER ECN 3541	26.9.80	
B		REV. PER ECN 3153	11.12.79	
A		REV. PER ECN 3090	24.10.78	
P	F	LTR	REVISION RECORD	APP DATE

		DWG SIZE		PART NO		DESCRIPTION		ITEM NO	
		← REVISION OF EACH ASSY NO (WRITE IN ANY CASE DWG REVISION)							
QTY REQD PER ASSY		PARTS LIST							
DIMENSIONS IN INCHES. TOLERANCES UNLESS OTHERWISE SPECIFIED:		MATERIAL		HEAT TREAT		FINISH			
2 PL DEC ±									
3 PL DEC ±.006 (±0.15)									
4 PL DEC ±									
ANGLES ±		DR 9.179 <i>ht</i>							
SURF TEXTURE: ✓		CHK 13.279 <i>Paul</i>							
REMOVE BURRS, BREAK SHARP EDGES .015R MAX		NAME		AMP MODU II PIN HEADER					
		SCALE		DWG NO		826634		SHEET REV H2	