







PART NUMBER	REV	FIRST USED	TYPE
2376800-1	A	-	NON CE
2376800-2	A	-	CE




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	6NOV20	CZ	



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	C.ZHU	6NOV20	 TE Connectivity	
DIMENSIONS: mm		CHK				
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		RBK-X1C HEAT SHRINK MACHINE		
MATERIAL		0 PLC	±	PRODUCT SPEC	SEE FIRST USED	
		1 PLC	±	APPLICATION SPEC	-	
		2 PLC	±	SIZE	A3	
		3 PLC	±	CAGE CODE		
		4 PLC	±	DRAWING NO	C=2376800	
		ANGLES	-	RESTRICTED TO		
		FINISH	-	SCALE	1:5	
				SHEET	1 OF 4	
				REV	A1	
				CUSTOMER DRAWING		

PART NUMBER	REV	FIRST USED	TYPE
2376800-1	A	-	NON CE
2376800-2	A	-	CE

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	6NOV20	CZ	





THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	C.ZHU	6NOV20		
DIMENSIONS: mm		CHK				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD			NAME	
0 PLC ±		PRODUCT SPEC	SEE FIRST USED		RBK-X1C HEAT SHRINK MACHINE	
1 PLC ±		APPLICATION SPEC	-		SIZE	A3
2 PLC ±		WEIGHT	-		CAGE CODE	
3 PLC ±					DRAWING NO	C=2376800
4 PLC ±					RESTRICTED TO	
ANGLES ±					SCALE	1:5
MATERIAL -					SHEET	2 OF 4
FINISH -					REV	A1
			CUSTOMER DRAWING			

C			
PART NUMBER	REV	FIRST USED	TYPE
2376800-1	A	-	NON CE
2376800-2	A	-	CE

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	6NOV20	CZ	

SPARE PARTS LIST

ITEM NO	-1	-2	TE/PN	DESCRIPTION
1	1	1	2234897-1	VIEW WINDOW
2	2	-	2234980-1	START BUTTON(GREEN)
3	2	2	2234984-1	CONTACT,START BUTTON
4	2	2	2234971-1	STORAGE BATTERY
5	10	10	2234981-X	PROCESS SLECTION BUTTON(X=BUTTON NUMBER,1.2.....)
6	1	1	2234973-1	"K"TYPE SOCKET
7	1	1	2234972-1	MOTOR DRIVER
8	2	-	2234988-1	PROXIMITY SENSOR,OMRON
9	1	1	2234840-1	EJECTOR BLADE LEFT
10	1	1	2234840-2	EJECTOR BLADE RIGHT
11	1	1	2234990-1	THERMOCOUPLE
12	1	-	2234963-1	COOLING FAN,220V
13	1	1	2234883-1	STEPPER MOTOR
14	1	1	2234887-1	CONNECTOR,ETHERNET
15	1	1	2234970-1	24V POWER SUPPLIER
16	1	1	2234969-1	SOLID STATE RELAY
17	1	1	2234983-1	EMERGENCY STOP BUTTON
18	1	-	2234985-1	SWITCH,TP-LINK
19	1	1	2234964-1	PLC
20	1	1	2234967-1	SAFETY REPLY
21	1	1	2234977-1	HUMAN MACHINE INTEFACE
22	1	1	2234968-1	TEMPERATURE CONTROLLER
23	2	2	2234868-1	RESET SPRING,LATCH ASSEMBLY
24	2	2	2234869-1	RESET SPRING,PINCH BLOCK
25	1	1	2234978-1	INLET, INCLUDES TWIN FUSEHOLDER,DOUBLE POLE SWITCH
26	1	1	2234991-1	HEATING ELEMENTS MOUDLE
27	-	1	2234967-2	TWO HANDED MOUDLE(FOR CE VERSION)
28	-	2	2234980-2	START BUTTON,CYCLE START PUSH BUTTON(WHITE)
29	1	2	2234969-2	SOLID STATE RELAY
30	1	-	2234995-1	FILTER FUSE TERMINAL
31	-	1	2234963-2	COOLING FAN,24V
32	-	1	2234985-2	SWITCH,KORENIX
33	-	1	2234995-2	WAVE FILTER
34	-	2	2234988-2	PROXIMITY SENSOR,RIKO



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	C.ZHU	6NOV20	 TE Connectivity				
DIMENSIONS: mm		CHK				RBK-X1C HEAT SHRINK MACHINE			
		APVD							
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC	SEE FIRST USED						
MATERIAL		APPLICATION SPEC	-		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
FINISH		WEIGHT	-		A3		C=2376800		
CUSTOMER DRAWING				SCALE	1:5	SHEET	3 OF 4	REV	A1

C			
PART NUMBER	REV	FIRST USED	TYPE
2376800-1	A	-	NON CE
2376800-2	A	-	CE

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	6NOV20	CZ	

SPARE PARTS LIST

ITEM NO	-1	-2	TE/PN	DESCRIPTION
35	1	1	4-2369604-5	CYLINDER,DETECTION UNIT
36	1	1	6-2369604-7	CYLINDER,CENTERING UNIT
37	2	2	5-2369604-8	SPRING,DETECTION UNIT
38	1	1	4-2369604-3	SPRING,COMPERSS TUBE
39	2	2	4-2369604-2	SPRING,SWING PIIECE
40	1	1	3-2369602-1	DETECT PIERCE
41	1	1	3-2369602-7	PLATE OF CENTER
42	1	1	3-2369604-5	LIGHT
43	1	1	7-2369602-1	MAIN DRIVE GEAR
44	1	1	5-2369602-7	DRIVEN GEAR
45	1	1	2-2369604-5	SENSOR,CENTER OFTUBE
46	1	1	8-2369602-1	MARK PLATE
47	2	2	2-2369603-4	POINTER
48	1	1	3-2369604-9	CALIBRATION LABEL
49	4	4	5-2369604-6	SENSOR,CYLINDER
50	1	1	6-2369602-5	DETECT PIERCE<SEE 3-2369602-1>
51	1	1	6-2369602-2	PLATE OF CENTER<SEE 3-2369602-7>

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.ZHU 6NOV20	 TE Connectivity		
DIMENSIONS: mm		CHK			
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		PRODUCT SPEC	RBK-X1C HEAT SHRINK MACHINE
MATERIAL -		FINISH -		APPLICATION SPEC	
				WEIGHT -	RESTRICTED TO
				SIZE A3	DRAWING NO C-2376800
		CUSTOMER DRAWING		SCALE 1:5	SHEET 4 OF 4 REV A1