

4

3





2

1

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
J			A	RELEASED	17JUN2010	C.O Y.N

本図面に記載された内容はタイコ エレクトロニクス アンプ(株)の所有する情報を開示しております。
無断で複写・配布する事を禁じます。 特許出願中

AS SHOWN : - 1



△ MATERIAL
ELEMENT : COPPER ALLOY
TRAY, GUIDE : STAINLESS
HOUSING : HIGH TEMPERATURE THERMO PLASTIC
UL94V-0 BLACK
△ FINISH
ELEMENT : CONTACT POINT: 0.4umMIN. Au
SOLDERING TINE SURFACE Au FLASH PLATE,
ALL OVER NICKEL PLATE 0.13umMIN.
ADD SEALING
3 COPLANARITY; 0.08MAX.

CAUTION; THERE IS A POSSIBILITY THAT NORMAL FORCE CHANGES ACCORDING TO THE PCB MATERIAL AND THICKNESS, ETC. PLEASE HANDLE IT WITH CARE.
当コネクタを実装する基板材質・厚さ等によって接圧変動する可能性がありますので、取り扱いに充分な注意をお願い致します。

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN C.OHASHI 17JUN2010	Tyco Electronics Tyco Electronics Corporation Kawasaki, Japan	
DIMENSIONS: 単位: 概 mm		CHK Y.NAKAZAWA 17JUN2010		
TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差 ±0.15 0-PLC ± 1-PLC ± 2-PLC ± 3-PLC ± 4-PLC ± ANGLES ±3°		APVD Y.NAKAZAWA 17JUN2010	NAME 名称 TS14-RVS DOUBLE CONTACT BODY ASSY	
MATERIAL 材料 SEE NOTE 1		PRODUCT SPEC 製品規格 108-78668	SIZE A300779	
FINISH 仕上 SEE NOTE 2		APPLICATION SPEC 取付適用規格 -	DRAWING NO 番号 C=2134034	
CUSTOMER DRAWING		WEIGHT 0.37g	RESTRICTED TO -	
			SCALE 尺度 X:1	
			SHEET 1 OF 4	
			REV A	

2		1					
LOC	DIST	REVISIONS 変更					
J		P	LTR	DESCRIPTION	DATE	DWN	APVD
			-	SEE SHEET 1	-	-	-

REFERENCE PCB LAYOUT
SCALE5:1

GENERAL TOLERANCE; ±0.05

△ HATCHING AREA; FORBIDDEN AREA OF PATTERN
△ NO PARTS LOCATED IN THIS AREA

D

D

C


C

B

B

A

A



本図面に記載された内容はタイコ エレクトロニクス アンプ(株)の所有する情報を開示しております。
無断で複写・配布する事を禁じます。 特許出願中

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN	
		CHK	
		APVD	
DIMENSIONS: 単位: ㎜		PRODUCT SPEC 製品規格	
		APPLICATION SPEC 取付適用規格	
		WEIGHT	
MATERIAL 材料		CUSTOMER DRAWING	
		SCALE 尺度	X:1
		SHEET 2	OF 4
		REV A	

Tyco Electronics Corporation Kawasaki, Japan		NAME 名称	
		TS14-RVS DOUBLE CONTACT BODY ASSY	
SIZE A3	CAGE CODE 00779	DRAWING NO 番号 C-2134034	RESTRICTED TO -

4


3

2

1


LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
J				SEE SHEET 1	-	-

D




D

C




C

B



B



A


AS SHOWN : - 1

A


THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		Tyco Electronics Corporation Kawasaki, Japan	
DIMENSIONS: 単位: ㎜		NAME 名称	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差 ±0.15		SIZE	
0 PLC ±		CAGE CODE	
1 PLC ±		DRAWING NO	
2 PLC ±		A300779C-2134034	
3 PLC ±		RESTRICTED TO	
4 PLC ±		-	
ANGLES ±3°		SCALE	
FINISH 仕上		X:1	
MATERIAL 材料		SHEET	
		3 OF 4	
		REV	
		A	

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	APVD
J			-	SEE SHEET 1	-	-

本図面に記載された内容はタイコ エレクトロニクス アンプ(株)の所有する情報を開示しております。
無断で複写・配布する事を禁じます。 特許出願中



METAL TRAY
P/N: 2134033-1



POSITION IN WHICH CONTACT
DEVIATE FROM SIM PAD
コンタクトがSIMカードPADを外れる位置

NOMINAL POSITION
通常使用時

TRAY EJECT POSITION
TARY引き出し位置

PAI CORT AREA
PAIコート材範囲

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:
単位: ㎜

MATERIAL
材料

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

一般公差 ±0.15

0-PLC ±

1-PLC ±

2-PLC ±

3-PLC ±

4-PLC ±

ANGLES ±3°

FINISH
仕上

DWN

CHK

APVD

PRODUCT SPEC
製品規格

APPLICATION SPEC
取付適用規格

WEIGHT

CUSTOMER DRAWING

Tyco Electronics Corporation
Kawasaki, Japan

NAME
名称

TS14-RVS
DOUBLE CONTACT
BODY ASSY

SIZE

CAGE CODE

DRAWING NO
番号

RESTRICTED TO

A300779

C=2134034

-

SCALE
尺度

X:1

SHEET
4

OF
4

REV
A