



Basic features

Approval/Conformity	CE WEEE
Basic standard	IEC 60947-5-2
Target material	Steel

Display/Operation

Function indicator	yes
Power indicator	no

Electrical connection

Connection	M12x1-Male, 4-pin, A-coded
Polarity reversal protected	yes
Protection against device mix-ups	yes
Short-circuit protection	yes

Electrical data

Load capacitance max. at Ue	0.15 µF
Min. operating current I _m	0 mA
No-load current I _o max., damped	10 mA
No-load current I _o max., undamped	10 mA
Operating voltage U _b	10...30 VDC
Output resistance R _a	Open collector
Pulse lengthening	2.5...250 ms
Rated insulation voltage U _i	75 V DC
Rated operating current I _e	200 mA
Rated operating voltage U _e DC	24 V
Rated short circuit current	100 A
Ready delay t _v max.	10 ms
Ripple max. (% of U _e)	15 %
Utilization category	DC -13
Voltage drop static max.	2 V

Environmental conditions

Ambient temperature	-25...70 °C
Contamination scale	3
EN 60068-2-27, Shock	Half-sinus, 30 g _n , 11 ms
EN 60068-2-6, Vibration	55 Hz, amplitude 1 mm, 3x30 min
IP rating	IP65

Functional safety

MTTF (40 °C)	1275 a
--------------	--------

Interface

Switching output	PNP normally open (NO)
------------------	------------------------

Inductive Sensors
BES IKV-010.23-G-Z-S4
Order Code: BES02TT

BALLUFF

Material

Housing material	Plastic
Material sensing surface	Plastic

Mechanical data

Dimension	80 x 45 x 20 mm
Pass-through	10.0 mm
Target size min.	Ball D = 2 mm

Remarks

After eliminating the overload, the sensor is functional again after a load-dependent delay time of 5-30 s.

Sensitivity adjustable

Static detection of metallic parts

Pulse lengthening adjustable.

For more information about MTTF and B10d see MTTF / B10d Certificate

Indication of the MTTF- / B10d value does not represent a binding composition and/or life expectancy assurance; these are simply experiential values with no warranty implications. These declared values also do not extend the expiration period for defect claims or affect it in any way.

Connector Drawings



Wiring Diagrams

