


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	RELEASED	03/31/10	DFP
B	ECN 8918 UPDATE PER VENDOR	09/18/17	B.PUCHASKI



PART NUMBER	CONNECTOR	AVAILABLE
HG914YE-NF	N-TYPE RECEPTACLE	STANDARD
HG914YE-NM	N-TYPE PLUG	STANDARD
HG914YE-RSP	RP SMA PLUG	STANDARD
HG914YE-SM	SMA PLUG	STANDARD

**NOTES:**

1. ANODIZED ALUMINUM CONSTRUCTION.
2. 900MHz 14Dbi
3. INDIVIDUALLY BOXED AND OEM LABEL PER PKG-00030/PKG-00021.

**REGULATORY COMPLIANCE:**  
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE		50 HIGH STREET NORTH ANDOVER, MA 01845
	DRAWN BY D. CASTRO	3/29/10		CATEGORY
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [5.1] .XXX = ±.005 [1.3]	CHECKED BY K. BLOMGREN	3/30/10		PRODUCT DESCRIPTION
	APPROVED BY K. BLOMGREN	3/30/10		CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY
PROJECTION	COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. <b>HG914YE</b>
		SCALE: NONE	CAD FILE: HG914YE.SLDDRW	SHEET 1 OF 1