



1) Sensing surface, 2) Sensor 1



Basic features

Application	Optimized response path especially suited for short-stroke cylinders.
Approval/Conformity	CE UKCA cULus WEEE
Basic standard	IEC 60947-5-2
Principle of operation	Magnetic field sensor
Trademark	Global

Display/Operation

Function indicator	yes
---------------------------	-----

Electrical connection

Cable	PUR, 0.3 m
Cable diameter D	2.50 mm
Connection	M12x1-Male, 4-pin, A-coded
Polarity reversal protected	yes
Protection against device mix-ups	yes
Short-circuit protection	yes

Electrical data

Assured switching field strength Ha	2 kA/m
Load capacitance max. at Ue	1 µF
No-load current I_o max., undamped	7 mA
Operating voltage U_b	10...30 VDC
Output resistance R_a	Open drain
Rated insulation voltage U_i	75 V DC
Rated operating current I_e	100 mA
Rated operating voltage U_e DC	24 V
Rated short circuit current	100 A
Rated switch field strength H_n	1.2 kA/m
Residual current I_r max.	80 µA
Ripple max. (% of U_e)	15 %
Switching frequency	7000 Hz
Turn-off delay t_{off} max.	0.07 ms
Turn-on delay t_{on} max.	0.07 ms
Utilization category	DC -13
Voltage drop static max.	2.5 V

Environmental conditions

Ambient temperature	-25...85 °C
Contamination scale	3
EN 60068-2-27, Shock	Half-sinus, 30 g _n , 11 ms
EN 60068-2-6, Vibration	55 Hz, amplitude 1 mm, 3x30 min
ESD	3A(8KV)
Emission	Group 1, Class B
IP rating	IP67

Magnetic Sensors
BMF 214K-PS-C-2A-SA95-S4-00,3
Order Code: BMF00A4



Functional safety

MTTF (40 °C) 520 a

Interface

Switching output PNP normally open (NO)

Material

Housing material PA 12
 Material jacket PUR

Mechanical data

Dimension 16.8 x 2.9 x 4.5 mm
 Mounting part C-slot
 SMC
 Bimba
 Schunk
 Tightening torque 0.03 Nm

Range/Distance

Temp. drift max. (% of Hn) 0.3 %

Remarks

Max. pull force on cable 10 N.

The sensor is functional again after the overload has been eliminated.

EMC: Surge resistance

External protection circuit is required. Document 825345, Section 2.

UL-MARKINGS: - For use in NFPA 79 Applications only - Adapters providing field wiring means are available from the manufacturer. Refer to manufacturers information.

For more information about MTTF and B10d see MTTF / B10d Certificate

Indication of the MTTF- / B10d value does not represent a binding composition and/or life expectancy assurance; these are simply experiential values with no warranty implications. These declared values also do not extend the expiration period for defect claims or affect it in any way.

Connector Drawings



Wiring Diagrams

