



1) Reference edge



### Basic features

Approval/Conformity	CE UKCA CCC WEEE
Basic standard	IEC 60947-5-1
Operating principle	1. Switch position: Mechanical
Version	Snap contact

### Display/Operation

Function indicator	1. Switch position: None
--------------------	--------------------------

### Electrical connection

Connection type	1. Switch position: Screw terminal
-----------------	------------------------------------

### Electrical data

Continuous current	1. Switch position: 0.1 A
Rated operating voltage Ue	1. Switch position: 250 V AC
Switching function mechanical	Single-pin changeover
Switching rate	1. Switch position: 200/min

### Environmental conditions

Ambient temperature	-5...85 °C
IP rating	IP67

### Functional safety

B10d (EN ISO 13849-1)	BSE 74.1: 10 mil. switching cycles
-----------------------	------------------------------------

### Material

Housing material	Aluminium, Anodized
Housing material, surface protection	Anodized
Material contacts	1. Switch position: Gold
Plunger material	1. Switch position: 1.4034 stainless steel

### Mechanical data

Approach direction	lateral or at right angles to mounting surface
Approach speed	1. Switch position: 20 m/min
Dimension	42 x 22 x 47 mm
Distance cam - reference edge	1. Switch position: 2.30...2.80 mm
Flange, feed-through	None
Installation	any
Life expectancy mechanical	1. Switch position: 10 mil. switching operations
Number of switching positions	Chisel Mechanical
Plunger spacing 1st switch position	11 mm
Plunger style	1st switch position: Chisel
Switch actuation force	1. Switch position: 8 N
Switching element	1. Switch position: BSE 74.1

### Range/Distance

Reproducibility	1. Switch position: $\pm 0.02$ mm
-----------------	-----------------------------------

## Wiring Diagrams

