



885231904	FC-FC SIM SM G655 2MM 10M	10000(+200/-0)
885231903	FC-FC SIM SM G655 2MM 5M	5000(+200/-0)
885231902	FC-FC SIM SM G655 2MM 3M	3000(+200/-0)
885231901	FC-FC SIM SM G655 2MM 2M	2000(+200/-0)
885231900	FC-FC SIM SM G655 2MM 1M	1000(+100/-0)
MX P/N	DESCRIPTION	LENGTH

NOTES:
 1. DUST CAPS ARE NOT SHOWN
 2. PER CHANNEL @ 1550nm
 IL <= 0.30dB
 RL > 50dB

ENTER DESCRIPTION
 EC NO: DG2008-0155
 DRWN: XPCHEN
 CHKD:
 APPR: JOWANG

2008/06/13
 2008/06/13
 2008/06/16

DESCRIPTION
 REV

QUALITY SYMBOLS
 =0
 =0

GENERAL TOLERANCES (UNLESS SPECIFIED)

	mm	INCH
4 PLACES	± ---	± ---
3 PLACES	± ---	± ---
2 PLACES	± ---	± ---
1 PLACE	± ---	± ---
ANGULAR ± ---°		

DRAFT WHERE APPLICABLE
 MUST REMAIN
 WITHIN DIMENSIONS

DIMENSION STYLE
MM ONLY

DRAWN BY: XP
 DATE: 2008/05/12

CHECKED BY: LISA
 DATE: 2008/05/12

APPROVED BY: JQWANG
 DATE: 2008/05/12

MATERIAL NO.
SEE TABLE

SIZE

SCALE: ---
 DESIGN UNITS: METRIC

THIRD ANGLE PROJECTION

TITLE: FC-FC SIM SM G655 2MM

MOLEX INCORPORATED

DOCUMENT NO.: SD-88523-009
 SHEET NO.: 1 OF 1

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION