



Technical drawing of a rectangular building footprint. The drawing shows a rectangle with dimensions and annotations. The top horizontal dimension is labeled $1.27 \cdot .05$. The right vertical dimension is labeled $2.54 \cdot .05$. The bottom horizontal dimension is labeled $\text{TYP. } 2.54 \cdot .05$. The bottom vertical dimension is labeled NON-ACCUM. . The drawing includes a dashed line representing a centerline or axis, with a dimension of $\varnothing 0.80 \cdot .08$ indicated. The drawing is labeled $\text{A} \cdot .08$ at the top center.



2	A
1	A

EC NO. Z2000-0171 DRAWN S. BARBIERI 26-04-00 CHK'D M. TESTAGUZZA 26-04-00 APPR'D R. MARTUCCI 26-04-00	DESCRIPTION MAJOR M SIGNIF. S CRITICAL C	QUALITY SYMBOLS	GENERAL TOLERANCES: (UNLESS SPECIFIED)		SCALE 5 : 1	DESIGN UNITS ☒ mm ☐ INCH	FIRST ANGLE PROJECTION	☐ mm ☐ INCH ☒ mm ONLY	REVISE ON CAD ONLY	
			mm	INCH	DRAWN BY & DATE S. BARBIERI 26-04-00		TITLE: ZOCCOLO PER ZIP - PASSO 2.54 ZIG - ZAG IN LINE PACKAGE ASSEMBLY - 2.54 / (.100) CENTERS -			
		4 PLACES	±0.	±.	CHECKED BY & DATE M. TESTAGUZZA 26-04-00		MOLEX MOLEX INCORPORATED			
		3 PLACES	±0.	±.	APPROVED BY & DATE R. MARTUCCI 26-04-00		MATERIAL NO. SEE CHART			
		2 PLACES	±0.	±.				DRAWING NO. SD-90510-001	SHEET NO. 1/2	
		1 PLACE	±0.	±.	ANGULAR: ±2° °	CAD FILENAME				
	REV	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.				SIZE A3



ZIP SOCKET
"HIGH COAT" VERSION

W/ H CODE	W/ H	A	B	C
PIN	CODE NO.			
10010 - 0110	10	27.75	19.85	21.25
10010 - 0120	20	27.85	24.12	26.67
10010 - 0124	24	27.94	27.21	31.75
10010 - 0130	30	28.00	29.27	36.83
10010 - 0140	40	28.25	45.52	52.67

EC NO. DRAWN CHKD APPR	DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)	SCALE	DESIGN UNITS	DRAWN BY & DATE	TITLE	FIRST ANGLE PROJECTION	DIMENSIONS: ☐ MM ☐ INCH ☐ ONLY	SHT	REV
		4 PLACES ±0.1	3 PLACES ±0.1	2 PLACES ±0.1	1 PLACE ±0.1						

ZIP SOCKET

"HIGH COAT" VERSION

Nº. DI CODICE P/N	Nº. VIE CCTS NO.	A	B	C
90510 · 0116	16	17.78	19.05	21.59
90510 · 0120	20	22.86	24.13	26.67
90510 · 0124	24	27.94	29.21	31.75
90510 · 0128	28	33.02	34.29	36.83
90510 · 0140	40	48.26	49.53	52.07

EC NO. Z2000-0171
DRWN: S. BARBIERI 26-04-00
CHK: M. TESTAGUZZA 26-04-00
APPR: R. MARTUCCI 26-04-00

QUALITY SYMBOLS	DESCRIPTION	REV
MAJOR M		
SIGNIF. S		
CRITICAL C		

GENERAL TOLERANCES: (UNLESS SPECIFIED)	
4 PLACES	±0.1
3 PLACES	±0.1
2 PLACES	±0.1
1 PLACE	±0.1
ANGULAR: ±2°	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	

SCALE 5 : 1	DESIGN UNITS ☒ mm ☐ INCH
DRAWN BY & DATE S. BARBIERI 26-04-00	
CHECKED BY & DATE M. TESTAGUZZA 26-04-00	
APPROVED BY & DATE R. MARTUCCI 26-04-00	
CAD FILENAME	

DIMENSIONS:		SHT	REV
☐ mm ☐ INCH	☒ mm ONLY		REVISE ON CAD ONLY
FIRST ANGLE PROJECTION			
TITLE: ZOCCOLO PER ZIP - PASSO 2.54 ZIG - ZAG IN LINE PACKAGE ASSEMBLY - 2.54 / (.100) CENTERS -			
MOLEX INCORPORATED			
MATERIAL NO. SEE CHART	DRAWING NO. SD-90510-001	SHEET NO. 2/2	
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.			SIZE A3