





ISO VIEW
(GREEN CODING)



COLOR: GREEN




COLOR: BLACK




COLOR: WHITE


OVERALL DIMENSIONS




B AXIS MATCHES WITH
THE FEMALE HOUSING AXIS



MINIMUM FREE AREA AVAILABLE
TO UNPLUG THE CONNECTOR






MALE TERMINALS SETTING




HEADER'S DEFINITION

GREEN CODING REPRESENTED



MALE TERMINALS VARIABLE SETTING



A	(1)	(63)		
REV.	FIRST	LAST	DELETED	SUPERSEDED
INSPECTION NUMBERS				

PRINT 1ST RELEASE




EC NO: G2012-0180	2012/04/18
DRWN:GDESBRUERES	2012/04/18
CH'KD:JDUCLDS	2012/04/18
APPR:OPIESSIS	2012/04/18

DESCRIPTION	QUALITY SYMBOL
	 = 0
	 = 0
	 = 0

GENERAL TOLERANCES (UNLESS SPECIFIED)		
	mm	INCH
4 PLACES	± .005	± .0004
3 PLACES	± .004	± .0003
2 PLACES	± .003	± .0002
1 PLACE	± .002	± .0001
0 PLACE	± .001	± .0001
ANGULAR ± 2 °		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		



DIMENSION STYLE	
MM ONLY	
DRAWN BY	DATE
GDESBRUERES	2012/04/18
CHECKED BY	DATE
JDCLOS	2012/04/18
APPROVED BY	DATE
OPLESIS	2012/04/23
MATERIAL NO.	
N/A	
SIZE	THIS DRAWING CONT INCORPORATED AND
A1	

SCALE 4:1	DESIGN UNITS METRIC		FIRST ANGLE PROJECTION
TITLE 3W INTERFACE 1.5 TERM. (FOR FEMALE HOUSING)			
molex			
DOCUMENT NO. SD-98845-003			SHEET NO. 1 OF 1
ALL INFORMATION THAT IS PROPRIETARY TO MOLEX SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			



CODING 4:1

HANDLING AREA




NOTE : 1 - The using conditions of the hinge are shown in the MOLEX specification n°AS-98821-001.

- 2 - Female terminal used : SCC RCPT TERM 1.5mm
 - Range 1 : 0988971109 (0.22 mm² to 2x0.22 mm²)
 - Range 2 : 0988971119 (0.5 mm² to 1 mm² included)
 - Range 3 : 0988971129 (2x0.5 mm² to 2 mm² included)


3 - Female connector will mate with male connector P/N 098822103x.

AREA REQUIRED WHEN THE CONNECTOR IS MATED






FIRST RELEASE EC No: G2007-0386 DRAWN: LPOUCHAUD 2008/03/10 CHKD: YIGEL 2008/03/10 APPR: LSTICKEIR 2008/03/10 REV A	DESCRIPTION QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM ONLY		SCALE 3:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
			mm	INCH	DRAWN BY LPOUCHAUD	DATE 2008/02/21	TITLE NSCC RCPT HSG 1.5 3CKT				
		4 PLACES	± ---	± ---	CHECKED BY YIGEL	DATE 2008/02/22					
		3 PLACES	± ---	± ---	APPROVED BY LSTICKEIR	DATE 2008/02/27	MOLEX INCORPORATED				
		2 PLACES	± 0.05	± ---	MATERIAL NO.		DOCUMENT NO.		SHEET NO.		
		1 PLACE	± 0.1	± ---	SEE CHART		SD-98817-002		1 OF 2		
		ANGULAR ± 1 °			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS						
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											


DATUM MONTH/YEAR



5



1:1




1:1

SUPPLIER ENGINEERING CONTROL ID

RAW MATERIAL

PRINT NUMBER

SUPPLIER MODIFICATION LEVEL



SUPPLIER PART NUMBER

GREEN CODING (P/N 0988171035) IS SHOWN.

NSCC Rcpt Hsg 1.5 3CKT		0988171035		Green	POLYESTER (PBT)	2.149 g		
		0988171031		Black				
		0988171030		White				
Description		Part-Number		Color	Raw Material	Weight effective		
FIRST RELEASE EC NO: G2007-0386 2008/03/10 2008/03/10 2008/03/10 DRAWN: LPOUCHAUD CHKD: YIGEL APPR: LSTICKEIR REV A	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 1:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION
						TITLE NSCC RCPT HSG 1.5 3CKT		
		4 PLACES ± ---		DRAWN BY LPOUCHAUD		DATE 2008/02/21		
		3 PLACES ± ---		CHECKED BY YIGEL		DATE 2008/02/22		
		2 PLACES ± 0.05		APPROVED BY LSTICKEIR		DATE 2008/02/27		
		1 PLACE ± 0.1		MATERIAL NO.		DOCUMENT NO.		
		ANGULAR ± 1 °		SIZE A2		SHEET NO. 2 OF 2		
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART SD-98817-002				
		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						