




MX150 2X2 BLADE SEALED ASSEMBLY MAT SEAL

BOM AND PIN OUT SHEET

ABBREVIATION	DESCRIPTION	COLOR	MATERIAL
A-BLACK	HOUSING, KEYING OPTION A	BLACK	SPS/NYLON GF20
B-LIGHT GRAY	HOUSING, KEYING OPTION B	LIGHT GRAY	SPS/NYLON GF20
C-BROWN	HOUSING, KEYING OPTION C	BROWN	SPS/NYLON GF20
D-GREEN	HOUSING, KEYING OPTION D	GREEN	SPS/NYLON GF20
C-DARK GRAY	HOUSING, KEYING OPTION C	DARK GRAY	SPS/NYLON GF20
D-STONE GRAY	HOUSING, KEYING OPTION D	STONE GRAY	SPS/NYLON GF20
A-YELLOW	HOUSING, KEYING OPTION A	YELLOW	SPS/NYLON GF20
GCP	GROMMET CAP (STANDARD PLUGGED)	BLACK	SPS/NYLON GF20
GCO	GROMMET CAP (STANDARD OPEN)	BLACK	SPS/NYLON GF20
PLR	PLR	NATURAL	SPS/NYLON GF20
M	MAT SEAL	ROYAL BLUE	INHERENTLY LUBRICATED SILICONE

FOR ADDITIONAL INFORMATION SEE SD-33482-0001










ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT				BLOCKED TERMINALS		STATUS	COMMENT	OPTIONAL ATTACHMENTS SOLD SEPARATELY	
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT				CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION					
		HOUSING KEY/COLOR	GROMMET CAP	PLR	MAT SEAL					BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS
MX150 ASSY BLD 2X2 BK A/4	334824001	A-BLACK	GCO	PLR	M	-	-	SALEABLE		N/A	N/A
						-	-				
MX150 ASSY BLD 2X2 LG B/4	334824002	B-LIGHT GRAY	GCO	PLR	M	-	-	SALEABLE		N/A	N/A
						-	-				
MX150 ASSY BLD 2X2 BR C/4	334824003	C-BROWN	GCO	PLR	M	-	-	NOT RECOMMENDED	SEE 334824103	N/A	N/A
						-	-				
MX150 ASSY BLD 2X2 GR D/4	334824004	D-GREEN	GCO	PLR	M	-	-	NOT RECOMMENDED	SEE 334824104	N/A	N/A
						-	-				
MX150 ASSY BLD 2X2 BK A/3	334824006	A-BLACK	GCP	PLR	M	-	2	SALEABLE		N/A	N/A
						-	-				
MX150 ASSY BLD 2X2 LG B/3	334824007	B-LIGHT GRAY	GCP	PLR	M	-	2	SALEABLE		N/A	N/A
						-	-				
MX150 ASSY BLD 2X2 BR C/3	334824008	C-BROWN	GCP	PLR	M	-	2	NOT RECOMMENDED	SEE 334824105	N/A	N/A
						-	-				
MX150 ASSY BLD 2X2 GR D/3	334824009	D-GREEN	GCP	PLR	M	-	2	NOT RECOMMENDED	SEE 334824106	N/A	N/A
						-	-				
MX150 ASSY BLD 2X2 BK A/2	334824011	A-BLACK	GCP	PLR	M	-	2	SALEABLE		N/A	N/A
						3	-				
MX150 ASSY BLD 2X2 LG B/2	334824012	B-LIGHT GRAY	GCP	PLR	M	-	2	SALEABLE		N/A	N/A
						3	-				
MX150 ASSY BLD 2X2 BR C/2	334824013	C-BROWN	GCP	PLR	M	-	2	NOT RECOMMENDED	SEE 334824107	N/A	N/A
						3	-				
MX150 ASSY BLD 2X2 GR D/2	334824014	D-GREEN	GCP	PLR	M	-	2	NOT RECOMMENDED	SEE 334824108	N/A	N/A
						3	-				
MX150 ASSY BLD 2X2 BK A/0	334824016	A-BLACK	GCP	PLR	M	1	2	SALEABLE		N/A	N/A
						3	4				
MX150 ASSY BLD 2X2 LG B/0	334824017	B-LIGHT GRAY	GCP	PLR	M	1	2	SALEABLE		N/A	N/A
						3	4				
MX150 ASSY BLD 2X2 BR C/0	334824018	C-BROWN	GCP	PLR	M	1	2	NOT RECOMMENDED	SEE 334824109	N/A	N/A
						3	4				
MX150 ASSY BLD 2X2 GR D/0	334824019	D-GREEN	GCP	PLR	M	1	2	NOT RECOMMENDED	SEE 334824110	N/A	N/A
						3	4				
MX150 ASSY BLD 2X2 BK A/1	334824021	A-BLACK	GCP	PLR	M	1	2	SALEABLE		N/A	N/A
						3	-				




MX150 2X2 BLADE SEALED ASSEMBLY MAT SEAL
BOM AND PIN OUT SHEET

ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT				BLOCKED TERMINALS		STATUS	COMMENT	OPTIONAL ATTACHMENTS SOLD SEPARATELY	
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT				CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION				BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS
		HOUSING KEY/COLOR	GROMMET CAP	PLR	MAT SEAL						
MX150 ASSY BLD 2X2 BK A/3	334824022	A-BLACK	GCP	PLR	M	-	-	SALEABLE		N/A	N/A
						-	4				
MX150 ASSY BLD 2X2 BK A/2	334824023	A-BLACK	GCP	PLR	M	-	-	SALEABLE		N/A	N/A
						3	4				
MX150 ASSY BLD 2X2 BK A/3	334824024	A-BLACK	GCP	PLR	M	-	-	SALEABLE		N/A	N/A
						3	-				
MX150 ASSY BLD 2X2 BK A/2	334824025	A-BLACK	GCP	PLR	M	1	2	SALEABLE		N/A	N/A
						-	-				
MX150 ASSY BLD 2X2 DG C/4	334824103	C-DARK GRAY	GCO	PLR	M	-	-	SALEABLE		N/A	N/A
						-	-				
MX150 ASSY BLD 2X2 SG D/4	334824104	D-STONE GRAY	GCO	PLR	M	-	-	SALEABLE		N/A	N/A
						-	-				
MX150 ASSY BLD 2X2 DG C/3	334824105	C-DARK GRAY	GCP	PLR	M	-	2	SALEABLE		N/A	N/A
						-	-				
MX150 ASSY BLD 2X2 SG D/3	334824106	D-STONE GRAY	GCP	PLR	M	-	2	SALEABLE		N/A	N/A
						-	-				
MX150 ASSY BLD 2X2 DG C/2	334824107	C-DARK GRAY	GCP	PLR	M	-	2	SALEABLE		N/A	N/A
						3	-				
MX150 ASSY BLD 2X2 SG D/2	334824108	D-STONE GRAY	GCP	PLR	M	-	2	SALEABLE		N/A	N/A
						3	-				
MX150 ASSY BLD 2X2 DG C/0	334824109	C-DARK GRAY	GCP	PLR	M	1	2	SALEABLE		N/A	N/A
						3	4				
MX150 ASSY BLD 2X2 SG D/0	334824110	D-STONE GRAY	GCP	PLR	M	1	2	SALEABLE		N/A	N/A
						3	4				
MX150 ASSY BLD 2X2 BK A/2	334824111	A-BLACK	GCP	PLR	M	-	2	SALEABLE		N/A	N/A
						-	4				
MX150 ASSY BLD 2X2 YW A/4	334824112	A-YELLOW	GCO	PLR	M	-	-	SALEABLE		N/A	N/A
						-	-				
MX150 ASSY BLD 2X2 LG B/3	334824113	B-LIGHT GRAY	GCP	PLR	M	1	-	SALEABLE		N/A	N/A
						-	-				
MX150 ASSY BLD 2X2 BK A/2	334824115	A-BLACK	GCP	PLR	M	1	-	SALEABLE		N/A	N/A
						3	-				
MX150 ASSY BLD 2X2 DG C/2	334824116	C-DARK GRAY	GCP	PLR	M	-	2	SALEABLE		N/A	N/A
						-	4				
MX150 ASSY BLD 2X2 LG B/2	334824117	B-LIGHT GRAY	GCP	PLR	M	-	2	SALEABLE		N/A	N/A
						-	4				
MX150 ASSY BLD 2X2 LG B/3	334824118	B-LIGHT GRAY	GCP	PLR	M	-	-	SALEABLE		N/A	N/A
						-	4				
MX150 ASSY BLD 2X2 BK A/2	334824119	A-BLACK	GCP	PLR	M	1	-	SALEABLE		N/A	N/A
						-	4				
MX150 ASSY BLD 2X2 BK A/3	334824120	A-BLACK	GCP	PLR	M	-	2	SALEABLE		N/A	N/A
						-	-				
MX150 ASSY BLD 2X2 BK A/1	334824121	A-BLACK	GCP	PLR	M	-	2	SALEABLE		N/A	N/A
						3	4				











SHEET DESCRIPTION	
CONFIGURATIONS	

		
2X2 - STANDARD (STD)	2X2 - UL V0*	
		
2X3 - STANDARD (STD)		2X3 - LENGTHENED
		
2X4 - STANDARD (STD)		
		
2X6 - STANDARD (STD)		
		
2X8 - STANDARD (STD)		
		
2X10 - STANDARD (STD)	2X10 - UL V0*	
DOCUMENT STATUS	P1	RELEASE DATE
		2018/02/16 22:02:26




UL V0 UNIQUE FEATURE
Partial1
SCALE 10:1

* MINOR GEOMETRY CHANGE THAN STANDARD CONFIGURATION.
SEE NOTE 2a FOR MORE INFORMATION


SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																			
 = 0	DIMENSION UNITS		SCALE		CURRENT REV DESC: EC NO: 171650 DRWN: PMANJUNATHAC 2018/01/03 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16 INITIAL REVISION: DRWN: APROFFITT 2014/04/28 APPR: VKOSHY 2014/05/14					molex										
	mm		1.5:1																	
 = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)									MX150 BLADE DUAL ROW SEALED ASSEMBLY MAT SEAL										
 = 0	ANGULAR TOL ± 1.0 °																			
 = 0	4 PLACES		±		PRODUCT CUSTOMER DRAWING															
 = 0	3 PLACES		±							DOCUMENT NUMBER		DOC TYPE		DOC PART	REVISION					
 = 0	2 PLACES		± 0.1		SD-33482-0001					PSD		001	E2							
 = 0	1 PLACE		± 0.2																	
 = 0	0 PLACES		±																	
 = 0	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES					MATERIAL NUMBER		CUSTOMER		SHEET NUMBER		
 = 0							A1-SIZE		33482							GENERAL MARKET		2 OF 11		

SHEET DESCRIPTION
KEY CONFIGURATIONS CONT.


2X6




KEY A



KEY B




KEY C




KEY D


2X8




KEY A




APPENDIX 1




100




KEY POINTS

 $2X$ 


KEY :



KEY I



KEY :










KFYI

SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																	
DIMENSION UNITS		SCALE		CURRENT REV DESC:				molex											
mm		3:1																	
GENERAL TOLERANCES (UNLESS SPECIFIED)		EC NO: 171650 DRWN: PMANJUNATHAC 2018/01/03 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16						MX150 BLADE DUAL ROW SEALED ASSEMBLY MAT SEAL											
ANGULAR TOL ± 1.0 °																			
	0	4 PLACES ±		INITIAL REVISION: DRWN: APROFFITT 2014/04/28 APPR: VKOSHY 2014/05/14				PRODUCT CUSTOMER DRAWING DOCUMENT NUMBER SD-33482-0001 DOC TYPE PSD DOC PART 001 REVISION E2											
	0.1	3 PLACES ±																	
	0.2	2 PLACES ±																	
	0.5	1 PLACE ±																	
	1.0	0 PLACES ±		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
	0.01					A1-SIZE		33482				GENERAL MARKET		4 OF 11					


SHEET DESCRIPTION	
BLADE SEALED ASSEMBLY	

CHARTED DIMENSION					
DESCRIPTION	DIMENSIONS				
	A	B	C	D	E
2X2	15.54	1.75	24.40	54.45	22.23
2X3 STANDARD	19.04	3.50	26.21	54.45	22.23
2X3 LENGTHENED	19.04	3.50	26.21	56.45	22.23
2X4	22.54	1.75	27.21	54.45	22.23
2X6	29.54	1.75	32.27	54.45	22.23
2X8	36.54	1.75	38.88	54.45	22.23
2X10	43.64	1.75	45.65	54.45	22.05



PRIMARY LOCK REINFORCEMENT (PLR) SHOWN
IN PRE-STAGED POSITION

SECTION W-W



PRIMARY LOCK REINFORCEMENT (PLR) SHOWN
IN FINAL-LOCK POSITION



SECTION V-V


SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION															
 = 0	DIMENSION UNITS		SCALE		CURRENT REV DESC:						molex					
	mm		3:1													
 = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 171650 DRWN: PMANJUNATHAC 2018/01/03 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16						MX150 BLADE DUAL ROW SEALED ASSEMBLY MAT SEAL					
 = 0																
 = 0	ANGULAR TOL ± 1.0 °				INITIAL REVISION: DRWN: APROFFITT 2014/04/28 APPR: VKOSHY 2014/05/14						PRODUCT CUSTOMER DRAWING					
 = 0	4 PLACES ±															
 = 0	3 PLACES ±				DOCUMENT NUMBER SD-33482-0001						DOC TYPE PSD		DOC PART 001		REVISION E2	
 = 0	2 PLACES ± 0.1															
 = 0	1 PLACE ± 0.2				MATERIAL NUMBER						CUSTOMER GENERAL MARKET				SHEET NUMBER 5 OF 11	
 = 0	0 PLACES ±															
 = 0	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING A1-SIZE		SERIES 33482							

DOCUMENT STATUS	P1	RELEASE DATE	2018/02/16 22:02:26
-----------------	----	--------------	---------------------

SHEET DESCRIPTION	
SYSTEM PACKAGING	

CHARTED DIMENSION				
CKT	BLADE CONFIGURATION	RECEPTACLE CONFIGURATION	DIMENSIONS	
			K	L
2X2	STANDARD	W/O CLIPSLOT	72.78	28.00
		W/ CLIPSLOT	72.78	28.50
		LENGTHENED	77.21	28.00
2X3	STANDARD	W/O CLIPSLOT	72.78	28.00
		W/ CLIPSLOT		30.50
	LENGTHENED	W/O CLIPSLOT	74.79	28.00
		W/ CLIPSLOT		30.50
2X4	STANDARD	W/O CLIPSLOT	72.78	29.50
		W/ CLIPSLOT		31.50
2X6	STANDARD	W/O CLIPSLOT	72.79	35.58
		W/ CLIPSLOT		
2X8	STANDARD	W/O CLIPSLOT	72.67	42.25
		W/ CLIPSLOT		
2X10	STANDARD	STANDARD	72.78	49.05



SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																			
	DIMENSION UNITS		SCALE		CURRENT REV DESC: EC NO: 171650 DRWN: PMANJUNATHAC 2018/01/03 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16 INITIAL REVISION: DRWN: APROFFITT 2014/04/28 APPR: VKOSHY 2014/05/14				molex MX150 BLADE DUAL ROW SEALED ASSEMBLY MAT SEAL											
	mm		4:1																	
	GENERAL TOLERANCES (UNLESS SPECIFIED)																			
	ANGULAR TOL ± 1.0 °								PRODUCT CUSTOMER DRAWING											
	4 PLACES		±										DOCUMENT NUMBER		DOC TYPE		DOC PART		REVISION	
	3 PLACES		±																	
	2 PLACES		± 0.1																	
	1 PLACE		± 0.2																	
	0 PLACES		±						SD-33482-0001				PSD		001		E2			
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS																			
THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER											SHEET NUMBER	
				A1-SIZE		33482				GENERAL MARKET		6 OF 11								


DOCUMENT STATUS	P1	RELEASE DATE	2018/02/16 22:02:26
-----------------	----	--------------	---------------------

SHEET DESCRIPTION
BACKSHELL NOTES


BACKSHELL NOTES: VALID UNLESS OTHERWISE SPECIFIED

1. GENERAL:


- a. APPLICATION SPECIFICATION SEE: AS-34951-001
- DESIGNED TO MATE WITH BLADE SEALED ASSEMBLY SPECIFIED IN MOLEX DRAWING SD-33482-0001.
 - SYSTEM TO BE USED WITH WIRE WITHIN DIAMETER RANGE OF 1.2mm TO 2.69mm.
 - COMPONENTS ARE OPTIONAL AND MUST BE PURCHASED SEPERATELY.
 - DESIGN IS OWNED BY SCHLEMMER FOR SCHLEMMER BACKSHELL.
 - DESIGN IS OWNED BY MOLEX FOR MOLEX BACKSHELL.
 - 90° ADAPTOR DESIGN IS OWNED BY MOLEX.
 - FOR ADDITIONAL INFORMATION SEE THE BACKSHELL COMPONENT DRAWING SD-34950-0001.




2X3




2X4




2X4



2X6



2X8



2X10

BACKSHELL CUSTOMER
MODEL NUMBER LEGEND

34950-XXXX


CUSTOMER MODEL COMPONENTS

- 0 - SCHLEMMER BACKSHELL ONLY
- 1 - SCHLEMMER BACKSHELL & MX150 HOUSING KEY A ASSEMBLY
- 2 - SCHLEMMER BACKSHELL & MX150 HOUSING KEY B ASSEMBLY
- 3 - SCHLEMMER BACKSHELL & MX150 HOUSING KEY C ASSEMBLY
- 4 - SCHLEMMER BACKSHELL & MX150 HOUSING KEY D ASSEMBLY
- 5 - MOLEX BACKSHELL ONLY
- 6 - MOLEX BACKSHELL & MX150 HOUSING KEY A ASSEMBLY
- 7 - MOLEX BACKSHELL & MX150 HOUSING KEY B ASSEMBLY
- 8 - MOLEX BACKSHELL & MX150 HOUSING KEY C ASSEMBLY
- 9 - MOLEX BACKSHELL & MX150 HOUSING KEY D ASSEMBLY

BACKSHELL FEATURES

- 1 - WITH RIBS
- 2 - WITHOUT RIBS
- 3 - 90° ADAPTOR

MX150 CIRCUIT SIZE 04, 06, 08, 12, 16, 20



90° ADAPTOR

BLADE SEALED ASSEMBLY






BACKSHELL (BKS)

SCALE 1.5:1


SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION										
	DIMENSION UNITS		SCALE		CURRENT REV DESC: EC NO: 171650 DRWN: PMANJUNATHAC 2018/01/03 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16 INITIAL REVISION: DRWN: APROFFITT 2014/04/28 APPR: VKOSHY 2014/05/14 THIRD ANGLE PROJECTION 			molex			
	mm		1.5:1								
	GENERAL TOLERANCES (UNLESS SPECIFIED)							MX150 BLADE DUAL ROW SEALED ASSEMBLY MAT SEAL			
	ANGULAR TOL ± 1.0 °										
	4 PLACES		±					PRODUCT CUSTOMER DRAWING DOCUMENT NUMBER SD-33482-0001 MATERIAL NUMBER CUSTOMER GENERAL MARKET DOC TYPE PSD SHEET NUMBER 7 OF 11			
	3 PLACES		±								
	2 PLACES		± 0.1								
	1 PLACE		± 0.2								
	0 PLACES		±								
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS							DRAWING A1-SIZE		SERIES 33482	









DOCUMENT STATUS	P1	RELEASE DATE	2018/02/16 22:02:26
-----------------	----	--------------	---------------------

SHEET DESCRIPTION	
SCHLEMMER BACKSHELL	




SECTION A-A



SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																
 = 0	DIMENSION UNITS		SCALE		CURRENT REV DESC:					molex MX150 BLADE DUAL ROW SEALED ASSEMBLY MAT SEAL							
	mm		3.5:1														
 = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)																
 = 0	ANGULAR TOL ± 1.0 °																
 = 0	4 PLACES		±		EC NO: 171650					PRODUCT CUSTOMER DRAWING							
 = 0	3 PLACES		±		DRWN: PMANJUNATHAC 2018/01/03												
 = 0	2 PLACES		± 0.1		CHK'D: MVANSLAMBROU 2018/02/16												
 = 0	1 PLACE		± 0.2		APPR: MVANSLAMBROU 2018/02/16					DOCUMENT NUMBER SD-33482-0001							
 = 0	0 PLACES		±		INITIAL REVISION:										DOC TYPE	DOC PART	REVISION
= 0	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES						MATERIAL NUMBER		CUSTOMER
							A1-SIZE		33482				GENERAL MARKET		8 OF 11		

DOCUMENT STATUS	P1	RELEASE DATE	2018/02/16 22:02:26
-----------------	----	--------------	---------------------




SHEET DESCRIPTION	
MOLEX BACKSHELL	



SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																
	DIMENSION UNITS		SCALE		CURRENT REV DESC: EC NO: 171650 DRWN: PMANJUNATHAC 2018/01/03 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16 INITIAL REVISION: DRWN: APROFFITT 2014/04/28 APPR: VKOSHY 2014/05/14			molex MX150 BLADE DUAL ROW SEALED ASSEMBLY MAT SEAL									
	mm		3:1														
	GENERAL TOLERANCES (UNLESS SPECIFIED)							PRODUCT CUSTOMER DRAWING									
	ANGULAR TOL ± 1.0 °																
	4 PLACES		±					DOCUMENT NUMBER SD-33482-0001					DOC TYPE	DOC PART	REVISION		
	3 PLACES		±										PSD	001	E2		
	2 PLACES		± 0.1					MATERIAL NUMBER					CUSTOMER GENERAL MARKET			SHEET NUMBER 9 OF 11	
	1 PLACE		± 0.2														
	0 PLACES		±					THIRD ANGLE PROJECTION		DRAWING A1-SIZE		SERIES 33482					
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS																

DOCUMENT STATUS	P1	RELEASE DATE	2018/02/16 22:02:26
-----------------	----	--------------	---------------------



SHEET DESCRIPTION	
SCHLEMMER BACKSHELL CONFIGURATIONS	





OVERALL MATED SYSTEM WITH BLADE AND RECEPTACLE BACKSHELL




OVERALL MATED SYSTEM WITH BLADE BACKSHELL



OVERALL MATED SYSTEM WITH RECEPTACLE BACKSHELL



BLADE SEALED ASSEMBLY WITH BLADE BACKSHELL




CHARTED DIMENSIONS							
CKT	BLADE CONFIGURATION	RECEPTACLE CONFIGURATION	DIMENSIONS				
			M	N	P	R	T
2X3	STANDARD	STANDARD	106.83	32.75	31.75	29.00	29.50
	LENGTHENED		108.71				
2X4	STANDARD	STANDARD	106.83	33.50	31.90	30.70	30.70
2X6	STANDARD	STANDARD	106.83	37.84	37.27	35.83	36.83


DOCUMENT STATUS	P1	RELEASE DATE	2018/02/16	22:02:26
-----------------	----	--------------	------------	----------

SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION													
	DIMENSION UNITS		SCALE		CURRENT REV DESC:					molex				
	mm		2:1											
	GENERAL TOLERANCES (UNLESS SPECIFIED)		EC NO: 171650 DRWN: PMANJUNATHAC 2018/01/03 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16 INITIAL REVISION: DRWN: APROFFITT 2014/04/28 APPR: VKOSHY 2014/05/14					MX150 BLADE DUAL ROW SEALED ASSEMBLY MAT SEAL						
	ANGULAR TOL ± 1.0 °													
	4 PLACES ±							PRODUCT CUSTOMER DRAWING						
	3 PLACES ±													
	2 PLACES ± 0.1													
	1 PLACE ± 0.2													
	0 PLACES ±		DOCUMENT NUMBER					DOC TYPE		DOC PART		REVISION		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER		
				A1-SIZE		33482				GENERAL MARKET		10 OF 11		


SHEET DESCRIPTION
MOLEX BACKSHELL CONFIGURATIONS




OVERALL MATED SYSTEM WITH BLADE AND RECEPTACLE BACKSHELL




(Ø DIM AA)
MIN PASS-THRU
WITH NO CLEARANCE




OVERALL MATED SYSTEM WITH BLADE BACKSHELL




(Ø DIM AB)
MIN PASS-THRU
WITH NO CLEARANCE




OVERALL MATED SYSTEM WITH RECEPTACLE BACKSHELL




(Ø DIM AC)
MIN PASS-THRU
WITH NO CLEARANCE




BLADE SEALED ASSEMBLY WITH BLADE BACKSHELL



(Ø DIM AD)
MIN PASS-THRU
WITH NO CLEARANCE



ADD THE VALUE OF 'Y' TO THE TOTAL DIMENSION
WHENEVER ADAPTOR IS USED



(Ø DIM AE)
MIN PASS-THRU
WITH NO CLEARANCE

CHARTED DIMENSIONS

CKT	BLADE CONFIGURATION	RECEPTACLE CONFIGURATION	DIMENSIONS									
			U	V	W	X	Y	AA	AB	AC	AD	AE
2X4	STANDARD	STANDARD	115.24	94.36	93.93	75.62	32.10	32.93	32.54	32.85	31.76	56.81
2X8	STANDARD	STANDARD	132.49	102.81	102.73	84.07	36.10	45.44	45.44	42.65	45.44	68.18
2X10	STANDARD	STANDARD	132.49	102.81	102.73	84.07	36.10	45.44	45.44	42.65	45.44	68.18

SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																
 = 0	DIMENSION UNITS		SCALE		CURRENT REV DESC:					molex							
	mm		1:1														
 = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 171650 DRWN: PMANJUNATHAC 2018/01/03 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16					MX150 BLADE DUAL ROW SEALED ASSEMBLY MAT SEAL							
 = 0																	
 = 0	ANGULAR TOL ± 1.0 °				INITIAL REVISION: DRWN: APROFFITT 2014/04/28 APPR: VKOSHY 2014/05/14					PRODUCT CUSTOMER DRAWING							
 = 0	4 PLACES		±														
 = 0	3 PLACES		±														
 = 0	2 PLACES		± 0.1														
 = 0	1 PLACE		± 0.2		THIRD ANGLE PROJECTION					DOCUMENT NUMBER		DOC TYPE		DOC PART		REVISION	
 = 0	0 PLACES		±							SD-33482-0001		PSD		001		E2	
 = 0	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS									DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER	
= 0							A1-SIZE		33482		GENERAL MARKET		11 OF 11				