

1) Optical axis receiver, 2) Output function



Basic features

Approval/Conformity	cULus CE UKCA WEEE
Basic standard	IEC 60947-5-2
Principle of operation	Photoelectric sensor
Series	Q08M
Style	Square Connection 90°

Electrical data

Load capacitance max. at Ue	0.05 µF
No-load current I _o max. at Ue	10 mA
Operating voltage U _b	10...30 VDC
Rated insulation voltage U _i	75 V DC
Rated operating current I _e	100 mA
Rated operating voltage U _e DC	24 V
Ready delay t _v max.	20 ms
Ripple max. (% of U _e)	10 %
Switching frequency	500 Hz
Turn-off delay t _{off} max.	1 ms
Turn-on delay t _{on} max.	1 ms
Utilization category	DC -13
Voltage drop U _d max. at I _e	0.7 V

Display/Operation

Display	Limit range - LED yellow, flashing LED yellow: Light received
---------	------------------------------------------------------------------

Electrical connection

Cable diameter D	3.00 mm
Cable length L	2 m
Conductor cross-section	0.14 mm ²
Connection	Cable, 2.00 m, PUR
Number of conductors	3
Polarity reversal protected	yes
Protection against device mix-ups	yes
Short-circuit protection	yes

Environmental conditions

Ambient temperature	-5...55 °C
EN 60068-2-27, Shock	Half-sinus, 30 gn, 11 ms, 3x6 Half-sinus, 100 gn, 2 ms, 3x8000
EN 60068-2-6, Vibration	10...55 Hz, amplitude 1 mm, 3x30 min 10...2000 Hz, amplitude 1 mm, 30 gn, 3x5 h
IP rating	IP67

Functional safety

MTTF (40 °C)	972.7 a
--------------	---------

Interface

Switching output PNP normally open (NO)

Material

Housing material Zinc, Die casting, nickel-plated
Material jacket PUR
Material sensing surface PMMA
Surface protection nickel-plated

Mechanical data

Dimension 8 x 44 x 8 mm
Mounting part Screw M3

Optical features

Principle of optical operation Through-beam sensor (receiver)
Switching function, optical dark-on

Range/Distance

Range 0...2.2 m
Rated operating distance Sn 2.2 m

Remarks

Order accessories separately.

For additional information, refer to user's guide.


Only for applications per NFPA 79 (machines with a supply voltage of maximum 600 V). Use an R/C (CYJV2) cable with suitable properties for attaching the device.

The sensor is functional again after the overload has been eliminated.

For more information about MTTF and B10d see MTTF / B10d Certificate

Indication of the MTTF- / B10d value does not represent a binding composition and/or life expectancy assurance; these are simply experiential values with no warranty implications. These declared values also do not extend the expiration period for defect claims or affect it in any way.

Wiring Diagrams



Opto Symbols

