

Basic features

Approval/Conformity	CE cULus UKCA WEEE
Principle of operation	Photoelectric sensor
Scope of delivery	Mounting bracket
Series	R81K
Style	Square with M18 Bullnose

Display/Operation

Adjuster	Potentiometer 270°
Display	Output function- LED yellow supply voltage - LED green
Setting	Sensitivity (Sn)

Electrical connection

Cable diameter D	3.9 mm
Cable length L	2 m
Connection	Cable, 2 m, PVC
Number of conductors	4
Polarity reversal protected	yes
Protection against device mix-ups	yes
Short-circuit protection	yes

Electrical data

No-load current I_0 max. at U_e	20 mA
Operating voltage U_b	10...30 VDC
Rated operating current I_e	200 mA
Rated operating voltage U_e DC	24 V
Ready delay t_v max.	100 ms
Voltage drop U_d max. at I_e	1 V

Environmental conditions

Ambient temperature	-15...60 °C
IP rating	IP67

Functional safety

MTTF (40 °C)	211 a
--------------	-------

Interface

Switching output	NPN normally open (NO)
------------------	------------------------

Material

Housing material	ABS PMMA
Material jacket	PVC
Material sensing surface	PMMA

Photoelectric Sensors
BOS R81K-NA-RD10-02
Order Code: BOS0295

BALLUFF

Mechanical data

Dimension	15 x 48.9 x 31 mm
Mounting part	Thread M18x1 Screw M3 (2x)


Range/Distance

Hysteresis H max.	20 %
Range	5...300 mm
Rated operating distance Sn	300 mm Adjustable

Optical features

Ambient light max.	10000 Lux
Light spot size	18 x 18 mm at 300 mm
Light type	LED, red light
Principle of optical operation	Diffuse sensor
Wave length	660 nm

Wiring Diagrams



Opto Symbols

