


REVISIONS			
REV	DESCRIPTION	DATE	APPV
A	PRODUCTION RELEASE	JHAGER 10/7/2021	



NOTES: (UNLESS OTHERWISE SPECIFIED)

- ALL DIMENSIONS ARE IN MILLIMETERS [IN].
- DIMENSIONS APPLY AFTER FINISHING.
- MANUFACTURE TO BE COMPLIANT WITH EU RoHS DIRECTIVE, USE MATERIALS THAT DO NOT CONTAIN REACH SUBSTANCES OF VERY HIGH CONCERN >1000ppm, AND USE DRC CONFLICT-FREE SOURCED MATERIALS.
- ELECTRICAL DATA SHOWN FOR REFERENCE ONLY. SEE LINX DATA SHEET FOR COMPLETE ELECTRICAL PROPERTIES.
- ANTENNAS QUALIFIED IAW LINX INTERNAL TEST PLAN AT LATEST REVISION.
- IMPEDANCE: 50Ω
- CONNECTOR: SMA TYPE INTERFACE IAW MIL-STD-348B
- OPERATING TEMP: -40°- +130°C
- FREQUENCY: MULTI-BAND [SEE DATASHEET]
- VSWR NTE 3.3 THROUGH ALL LTE BANDS
- PACKAGE UNIT INDIVIDUALLY BEFORE PLACING IN LOT BAG.
- WEIGHT 10g.
- LABELING TO INCLUDE THE FOLLOWING INFORMATION ONLY ON LOT BAG AND BOXES:
 - LOT NUMBER
 - LINX PART NUMBER
 - QUANTITY
 - COUNTRY OF ORIGIN

WARNING: THIS DRAWING CONTAINS PROPRIETARY INFORMATION THAT IS THE SOLE PROPERTY OF LINX TECHNOLOGIES, AND SHALL BE TREATED AS SUCH. NO DISCLOSURE OR REPRODUCTION OF THIS DOCUMENT IS PERMITTED, IN WHOLE OR IN PART, WITHOUT THE EXPRESS WRITTEN PERMISSION OF LINX TECHNOLOGIES OR ITS DESIGNATED AGENTS.



159 ORT LANE
MERLIN, OR 97532

TITLE:
**ANTENNA LTE MON
SMA POSITIONABLE**

MATERIAL: VAR BRASS	INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5.		PROJECTION:
	.X ±2.0 .XX ±1.00 .XXX ±.500	ANGLES: ±1° SURFACE:	
FINISH: BLACK NICKEL	DRAWN: SHOGAN	DT: 10/17/19	
	ENGR: DASARATHAN	DT:	

SIZE	DWG. NO.	REV
A	C-ANT-LTE-MON-SMA-L	A
SCALE: 1:1	DO NOT SCALE DRAWING	SHEET 1 OF 1