



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
 © COPYRIGHT 20 BY - ALL RIGHTS RESERVED.



REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
A		INITIAL RELEASE	23SEP2022	VL SZH





1-2386331-2 AS SHOWN
SCALE 2:1



- ① CAGE ASSEMBLY: STAINLESS STEEL.
EMI SPRING: COPPER ALLOY/NICKEL PLATING.
- ② REFERENCE APPLICATION SPECIFICATION 114-32023 FOR RECOMMENDED DRILL HOLE DIAMETER AND PLATING THICKNESS. BOARD LAYOUT PER THIS PRINT.
- ③ DATUM AND BASIC DIMENSION ESTABLISHED BY CUSTOMER.
- ④ PART NUMBER AND DATE CODE (YYWWD) MARKED APPROXIMATELY AS SHOWN.
- 5. MATES WITH QSFP DD MSA COMPATIBLE TRANSCEIVER.
- 6. MINIMUM PC BOARD THICKNESS: SINGLE SIDED: 1.57 MIN
DOUBLE SIDED: 3.00 MIN
- ⑦ DIMENSION APPLIES WITH MODULE INSERTED INTO CAGE



SCALE 2:1




CLOSED TOP	0	1-2386331-1
HS OPENING	0	1-2386331-5
CLOSED TOP	2 PER PORT	2386331-1
HS OPENING	2 PER PORT	1-2386331-2
REMARK	REAR PIN#	PART NUMBER


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN VINDY LIU 02NOV2021	TE Connectivity	
		CHK - 02NOV2021		
DIMENSIONS: mm		APVD - 02NOV2021	NAME CAGE ASSEMBLY, QSFP112, STANDARD	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC 108-60122	WITH EMI SPRING, 1X2	
0 PLC ±0.25	1 PLC ±0.25	APPLICATION SPEC 114-60025	SIZE A2	CAGE CODE -
2 PLC ±0.20	3 PLC ±0.10	WEIGHT -	DRAWING NO C-2386331-C	RESTRICTED TO -
4 PLC ±	ANGLES ±	CUSTOMER DRAWING	SCALE 1:1	SHEET 1 OF 6
FINISH				REV A

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
 © COPYRIGHT 20 BY - ALL RIGHTS RESERVED.


REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
-	-	SEE SHEET 1	-	-




1-2386331-2 AS SHOWN
 WITH HS OPENING
 AND 2 REAR PINS
 SCALE 2:1




1-2386331-5 AS SHOWN
 WITH HS OPENING
 AND 0 REAR PINS
 SCALE 2:1



1-2386331-1 AS SHOWN
 W/ CLOSED TOP
 AND 0 REAR PINS
 SCALE 2:1




2386331-1 AS SHOWN
 W/ CLOSED TOP
 AND 2 REAR PINS
 SCALE 2:1


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 02NOV2021 VINDY LIU	 TE Connectivity															
DIMENSIONS: mm		CHK 02NOV2021			NAME CAGE ASSEMBLY, QSFP112, STANDARD													
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 02NOV2021	PRODUCT SPEC 108-60122	RESTRICTED TO														
<table border="0"> <tr> <td>0 PLC</td> <td>±0.25</td> </tr> <tr> <td>1 PLC</td> <td>±0.25</td> </tr> <tr> <td>2 PLC</td> <td>±0.20</td> </tr> <tr> <td>3 PLC</td> <td>±0.10</td> </tr> <tr> <td>4 PLC</td> <td>±</td> </tr> <tr> <td>ANGLES</td> <td>±</td> </tr> <tr> <td>FINISH</td> <td>±</td> </tr> </table>		0 PLC	±0.25	1 PLC	±0.25	2 PLC	±0.20	3 PLC	±0.10	4 PLC	±	ANGLES	±	FINISH	±	APPLICATION SPEC 114-60025	SIZE A2	CAGE CODE -
0 PLC	±0.25																	
1 PLC	±0.25																	
2 PLC	±0.20																	
3 PLC	±0.10																	
4 PLC	±																	
ANGLES	±																	
FINISH	±																	
MATERIAL	-	WEIGHT	DRAWING NO C-2386331-C	SCALE 1:1														
-		CUSTOMER DRAWING	SHEET 2 OF 6	REV A														

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
 © COPYRIGHT 20 BY - ALL RIGHTS RESERVED.


REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
-	-	SEE SHEET 1	-	-




CAGE ASSEMBLY OMITTED FOR CLARITY



SINGLE SIDE MOUNTING



CAGE ASSEMBLY OMITTED FOR CLARITY






BELLY TO BELLY MOUNTING

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN VINDY LIU 02NOV2021	TE Connectivity	
		CHK - 02NOV2021		
DIMENSIONS: mm		APVD - 02NOV2021	NAME CAGE ASSEMBLY, QSFP112, STANDARD	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC 108-60122	WITH EMI SPRING, 1X2	
0 PLC ±0.25	1 PLC ±0.25	APPLICATION SPEC 114-60025	SIZE A2	CAGE CODE -
2 PLC ±0.20	3 PLC ±0.10	WEIGHT -	DRAWING NO C-2386331-C	RESTRICTED TO -
4 PLC ±	ANGLES ±	CUSTOMER DRAWING	SCALE 1:1	SHEET 3 OF 6
FINISH -	-			REV A

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
 © COPYRIGHT 20 BY - ALL RIGHTS RESERVED.



REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
-	-	SEE SHEET 1	-	-



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN VINDY LIU 02NOV2021	TE Connectivity	
		CHK - 02NOV2021		
DIMENSIONS: mm		APVD - 02NOV2021	NAME CAGE ASSEMBLY, QSFP112, STANDARD	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC 108-60122	WITH EMI SPRING, 1X2	
0 PLC ±0.25	1 PLC ±0.25	APPLICATION SPEC 114-60025	SIZE A2	CAGE CODE -
2 PLC ±0.20	3 PLC ±0.10	WEIGHT -	DRAWING NO C-2386331-C	RESTRICTED TO -
4 PLC ±	ANGLES ±	CUSTOMER DRAWING	SCALE 1:1	SHEET 4 OF 6
MATERIAL -	FINISH -			REV A


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
 © COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



DETAIL D
SCALE 4:1

RECOMMENDED PCB LAYOUT
BELLY TO BELLY
SCALE 3:1




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN VINDY LIU 02NOV2021	TE Connectivity		
		CHK - 02NOV2021			
		APVD - 02NOV2021	NAME CAGE ASSEMBLY, QSFP112, STANDARD		
DIMENSIONS: mm		PRODUCT SPEC 108-60122		WITH EMI SPRING, 1X2	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC 114-60025		RESTRICTED TO	
0 PLC ±0.25		WEIGHT -		SIZE A2	
1 PLC ±0.25		CUSTOMER DRAWING		CAGE CODE -	
2 PLC ±0.20		SCALE 1:1		DRAWING NO C-2386331-C	
3 PLC ±0.10		SHEET 5 OF 6		REV A	
4 PLC ±					
ANGLES ±					
FINISH -					

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
 © COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

PCB LAYOUT RECOMMENDATION FOR 0 REAR PIN SOLUTION
 UNSPECIFIED DIMENSIONS PLEASE REFER PAGE 4&5



RECOMMENDED PCB LAYOUT
 W/ 0 REAR PIN
 SCALE 3:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN VINDY LIU 02NOV2021	TE Connectivity																
		CHK - 02NOV2021																	
		APVD - 02NOV2021	NAME CAGE ASSEMBLY, QSFP112, STANDARD																
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC 108-60122															
<table border="0"> <tr><td>0 PLC</td><td>±0.25</td></tr> <tr><td>1 PLC</td><td>±0.25</td></tr> <tr><td>2 PLC</td><td>±0.20</td></tr> <tr><td>3 PLC</td><td>±0.10</td></tr> <tr><td>4 PLC</td><td>±</td></tr> <tr><td>ANGLES</td><td>±</td></tr> <tr><td>FINISH</td><td>±</td></tr> </table>		0 PLC	±0.25	1 PLC	±0.25	2 PLC	±0.20	3 PLC	±0.10	4 PLC	±	ANGLES	±	FINISH	±	APPLICATION SPEC 114-60025		SIZE A2	
0 PLC	±0.25																		
1 PLC	±0.25																		
2 PLC	±0.20																		
3 PLC	±0.10																		
4 PLC	±																		
ANGLES	±																		
FINISH	±																		
MATERIAL - -		WEIGHT -		CAGE CODE -															
		CUSTOMER DRAWING		DRAWING NO C-2386331-C															
		SCALE 1:1		RESTRICTED TO -															
		SHEET 6 OF 6		REV A															