


© 2023 TE Connectivity. All Rights Reserved.

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
1		NEW DRAWING	25MAY2023	DC	JH
2		UPDATE NOTE TYPO	15JUN2023	DC	JH
A		GTP ECN-23-220502	04JUL2023	DC	JH

CONN. FACE DOWN



SCALE 3:2


A ± 3





(1.13)

ASSEMBLY NOTES:

- FABRICATE TO MEET IPC - 6013, CLASS 2.
INSPECT TO MEET IPC - A - 600, CLASS 2.
- MATERIAL
A. PI FILM+VHB AHDESIVE
B. CABLE : COAX CABLE DIA 1.13 CONN. I-PEX, OR EQUIVAKENT.
- FINISH:
A. SOLDERMASK BOTH SIDES: ORANGE
- GENERAL TOLERANCE +/- 0.2
- PACKAGE : SINGULATED PARTS TO BE SECURELY BAG WRAPPED, BAGGED OR VACUM PACKED IN BULK.
- CONSULT TE CONNECTIVITY DSL000551
- SILKSCREEN; WHITE EPOXY INK
A. TE LOGO. P/N
B. WORD REV, FOLLOWED BY LATEST REVISION LETTER AS SHOWN
C. 4 DIGIT DATE CODE : FIRST 2 DIGITS FOR THE WEEK CODE AND 2ND 2 DIGITS FOR THE YEAR CODE.
OTHERS: SPECIFIC TE SOURCE CODE NUMBER DIGITS AS REQUIRED



MHF 4L	150.00	L000551-06
	100.00	L000551-05
	50.00	L000551-04
MHF	150.00	L000551-03
	100.00	L000551-02
	50.00	L000551-01
CONNECTOR TYPE	"A"	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	25MAY2023	 TE Connectivity		
DIMENSIONS: mm		CHK	20JUN2023			
		APVD	20JUN2023			
		TOLERANCES UNLESS OTHERWISE SPECIFIED:				
MATERIAL TBD material_2		FINISH	-	NAME FPC ANT, VDP, 868HMz		
		0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±-		PRODUCT SPEC	-	
		-		APPLICATION SPEC	-	
		-		WEIGHT	-	
		-		SIZE	A3	CAGE CODE 00779
		-		DRAWING NO	G=L000551	
		-		RESTRICTED TO	-	
		-		CUSTOMER DRAWING	SCALE 1:1	SHEET 1 OF 1
		-		REV	A	