





P	LTR	DESCRIPTION	DATE	DWN	APVD
1		NEW DRAWING	25MAY2023	DC	JH
2		UPDATE NOTE TYPO	15JUN2023	DC	JH
A		GTP ECN-23-220502	04JUL2023	DC	JH

ASSEMBLY NOTES:

- FABRICATE TO MEET IPC - 6013, CLASS 2.  
INSPECT TO MEET IPC - A - 600, CLASS 2.
- MATERIAL
  - PI FILM+VHB AHDESIVE
  - CABLE : COAX CABLE DIA 1.13 CONN. I-PEX, OR EQUIVAKENT.
- FINISH:
  - SOLDERMASK BOTH SIDES: ORANGE
- GENERAL TOLERANCE +/- 0.2
- PACKAGE : SINGULATED PARTS TO BE SECURELY BAG WRAPPED, BAGGED OR VACUM PACKED IN BULK.
- CONSULT TE CONNECTIVITY DSL000558
- SILKSCREEN; WHITE EPOXY INK
  - TE LOGO. P/N
  - WORD REV, FOLLOWED BY LATEST REVISION LETTER AS SHOWN
  - 4 DIGIT DATE CODE : FIRST 2 DIGITS FOR THE WEEK CODE AND 2ND 2 DIGITS FOR THE YEAR CODE.  
OTHERS:SPECIFIC TE SOURCE CODE NUMBER DIGITS AS REQUIRED



A±3



SCALE 2:1

MHF 4L	150.00	L000558-06
	100.00	L000558-05
	50.00	L000558-04
MHF	150.00	L000558-03
	100.00	L000558-02
	50.00	L000558-01
CONNECTOR TYPE	"A"	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DC 24MAY2023	TE Connectivity NAME FPC ANT,HDP, 868HMz	
DIMENSIONS: mm		CHK SJ 24MAY2023		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD JH 24MAY2023		
0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±-		PRODUCT SPEC -		
MATERIAL TBD material_2	FINISH - finish_spec_2	APPLICATION SPEC -	WEIGHT -	SIZE A3
		CUSTOMER DRAWING	SCALE 1:1	CAGE CODE 00779
				DRAWING NO C=L000558
				RESTRICTED TO -
				SHEET 1 OF 1
				REV A