

## Basic features

Approval/Conformity	CE cULus WEEE
---------------------	---------------------

## Display/Operation

Function indicator (Pin 4)	LED yellow
Power indicator	Green LED

## Electrical connection

Bending radius min., fixed cable	5 x D
Bending radius min., flexible cable	10 x D
Cable	PUR black, 10 m, drag chain compatible
Cable diameter D	4.70 mm ±0.20 mm
Cable, bending cycles min.	5 mil.
Conductor cross-section	0.34 mm <sup>2</sup>
Connection	M8x1-Female, angled, 4-pin, A-coded
Connector configuration	right-angle
Number of conductors	4
Number of pins	4
System	Molded

## Electrical data

Operating voltage U <sub>b</sub>	30 VDC
Rated current (40 °C)	4.0 A

## Environmental conditions

Cable temperature UL max., fixed routing	80 °C
Cable temperature UL max., flexible routing	80 °C
Cable temperature, drag chain	-25...60 °C
Cable temperature, fixed routing	-50...90 °C
Cable temperature, flexible routing	-25...90 °C
IP rating	IP67, IP69K

## Interface

Switching output	PNP NO/NC antivalent
------------------	----------------------

## Material

Cable jacket, material	PUR
Material contact carrier	PUR
Material contacts	Bronze
Material cover nut	Die-cast zinc or nickel plated brass
Material grip	PUR

## Mechanical data

Acceleration max., drag chain	5 m/s <sup>2</sup>
Cable jacket, color	black
Cable length L	10.00 m
Cable properties	drag chain compatible
Horizontal travel permitted, drag chain	5 m
Tightening torque pigtail	0.4 Nm
Traverse speed max., drag chain	200 m/min
Vertical travel permitted, drag chain	5 m

Single-Ended Cordsets  
**BCC M324-0000-10-008-PX0434-100**  
Order Code: **BCC02NA**

**BALLUFF**

Remarks


Cable construction acc. to UL-AWM Style 20549  
Halogen-free per DIN VDE 0472 Part 815  
Silicone-free  
Flame-retarding acc. to IEC 60332-2  
Enclosure rating per IEC 60529 or 20653, only in screwed state with the associated mating piece.

**Connector Drawings**



PIN 1: brown  
PIN 2: white  
PIN 3: blue  
PIN 4: black

**Wiring Diagrams**



1) Green LED = Power  
2) Yellow LED = Function