



1) Sensing surface



### Basic features

Antenna type	round
Approval/Conformity	CE UKCA cULus WEEE
EN 55011	Size 1, Cl. A
Principle of operation	Data carrier

### Electrical data

Data retention time/years	≥ 10
Memory organization	64 × 8 bits
Programming cycles	Unlimited
Programming time	for 64x8 bits: 1.1s for 1x8 bits: 0.45s
Read cycles	Unlimited
Read time	for 64x8 bits: 0.33 s

### Environmental conditions

Ambient temperature	-30...70 °C
Continuous shock load	yes
EN 60068-2-27, Shock	yes
EN 60068-2-32 Free fall	yes
EN 60068-2-6, Vibration	yes
IP rating	IP67
Storage temperature	-30...85 °C

### Functional Characteristics

Memory type	EEPROM
User data, read/write	8192 Byte

### Material

Housing material	Brass, nickel-plated
Housing material, surface protection	nickel-plated

### Mechanical data

Application weight	66.00 g
Dimension	Ø 30 x 35 mm
Installation	metal-free (clear zone) on metal flush in metal
Size	M30x1.5

LF (70/455 kHz)  
**BIS C-104-32/A**  
**Order Code: BIS0007**

**BALLUFF**

**Remarks**

---

Time specification includes data check.  
For installation requirements see corresponding read/write head.  
Only together with converter BIS C-901 or BIS C-6xx and the appropriate read/write head.  
Values are under rated conditions unless otherwise specified.