

Basic features

Approval/Conformity	CE UKCA cULus WEEE
Scope of delivery	Part label (20x) Port cover M12 (4x) Grounding strap Lock washer Short guide M4x6 screw
Style	Two-row

Display/Operation

Actuator supply UA, indicator	Green LED
IO-Link communication indicator	Green LED
Module supply indicator	Green LED
Sensor supply US indicator	Green LED
Switching function display	LED yellow

Electrical connection

Connection (COM 1)	M12x1-Male, 4-pin, A-coded
Connection slots	8x M12x1-Female, 5-pin, A-coded
Contact, surface protection	nickel plated 2 µm/gold plated 0.4 µm

Electrical data

Configurable inputs/outputs	yes
Current consumption without load, max.	50 mA
Current sum UA, actuator	4 A
Current sum US, sensor	4 A
IO-Link function	Device
IO-Link ports, number	1
Operating voltage Ub	18...30.2 VDC
Rated operating voltage Ue DC	24 V
Switching current	16x 200 mA

Environmental conditions

Ambient temperature	-5...55 °C
EN 60068-2-6, Vibration	5...61 Hz, constant amplitude 1 mm 61...500 Hz, constant acceleration 15 g
IP rating	IP67, when threaded in
Storage temperature	-25...70 °C

Functional safety

MTTF (40 °C)	38.7 a
---------------------	--------

IO-Link

IO-Link Profil IDs	N/A
---------------------------	-----

Interface

Cycle time min.	6.2 ms
Digital inputs	16x PNP, Type 3
Digital outputs	16x PNP
Extension port	yes
IO-Link version	1.1
Interface	IO-Link 1.1
Process data IN	8 bytes
Process data OUT	2 bytes
Process data cycle min.	6.2 ms
Single-channel monitoring	yes
Transfer rate	COM2 (38.4 kBaud)

Material

Gasket, material	FKM 75
Housing material	Zinc, Die casting
Housing shield	yes
Surface protection	Cu 15 µm Ni 15 µm

Mechanical data


Dimension	68 x 31.8 x 181.5 mm
Mounting ground strap	M4 internal thread
Mounting part	2-hole screw mount

Remarks

See short guide

For more information about MTTF and B10d see MTTF / B10d Certificate

Indication of the MTTF- / B10d value does not represent a binding composition and/or life expectancy assurance; these are simply experiential values with no warranty implications. These declared values also do not extend the expiration period for defect claims or affect it in any way.

Connector Drawings


IO-Link

PIN 1: +24V

PIN 2: +24V

PIN 3: GND

PIN 4: C/Q, IO-Link DC-Channel



I/O ports

PIN 1: +24V

PIN 2: Input/Output 2

PIN 3: GND

PIN 4: Input/Output 1

PIN 5: Function ground