



- 1) LED Power, 2) LED function indicator, 3) 4x operating keys, 4) LED N.C. function active, 5) 7x seven-segment display, 7) Plug connection sensor, 8) DIN rail mount 35mm, 9) Flap



## Basic features

Approval/Conformity	CE UKCA cULus WEEE
Basic standard	IEC 60947-5-2
Series	BAE

## Display/Operation

Adjuster	Key (4x)
Function indicator	yes
Power indicator	yes
Setting	Sensitivity (Sn) Time function on/off Switching or analog Teaching switchpoints Various switching modes Dynamic function External teach function

## Electrical connection

Cable diameter D	4.50 mm
Cable length L	0.3 m
Connection	M12x1
Polarity reversal protected	yes
Protection against device mix-ups	yes
Short-circuit protection	yes

## Electrical data

Load capacitance max. at $U_e$	0.33 $\mu$ F
Load resistance $R_L$ max. (Analog I)	400 ohms
Load resistance $R_L$ min. (Analog V)	1 kOhm
No-load current $I_o$ max. at $U_e$	25 mA
Operating voltage $U_b$	15...30 VDC
Rated insulation voltage $U_i$	75 V DC
Rated operating current $I_e$	50 mA
Rated operating voltage $U_e$ DC	24 V
Ready delay $t_v$ max.	200 ms
Residual current $I_r$ max.	10 $\mu$ A
Switching frequency	100 Hz
Utilization category	DC -13
Voltage drop $U_d$ max. at $I_e$	2 V

## Environmental conditions

Ambient temperature	-10...70 °C
IP rating	IP40

## Functional safety

MTTF (40 °C)	252 a
--------------	-------

## Interface

Analog output	Analog, voltage/Analog, current 0...10 V/4...20 mA
Switching output	PNP/NPN NO/NC programmable
Time function	On/off delay time programmable

Capacitive Sensors  
**BAE SA-CS-026-YP-BP00,3-GS04**  
**Order Code: BAE00LA**



**Material**

Cover cap material	PA
Cover material	PBT
Housing material	PBT
Material jacket	PUR

**Mechanical data**

<b>Dimension</b>	10.5 x 45 x 75.5 mm
<b>Mounting part</b>	DIN EN-50045 rail 15 mm
	DIN EN-50022 rail 35 mm
	Screw M3

**Remarks**

Please observe EMC-conformal cable routing. All measuring and norm vales in the data sheet are referenced to 2 m single-ended cordset.  
 max. load current: 50mA with UL approval, <50 to 100mA possible, but without UL approval  
 The connection to the connector must use a listed cable assembly (CYJV) with a minimum value of 80°C  
 The potentiometer does not have a fixed stop, but can be turned endlessly without destroying anything.  
 If no change in the switching signal is detected, the potentiometer should be turned forwards or backwards until a signal change occurs at the output.  
 For more information about MTTF and B10d see MTTF / B10d Certificate

Indication of the MTTF- / B10d value does not represent a binding composition and/or life expectancy assurance; these are simply experiential values with no warranty implications. These declared values also do not extend the expiration period for defect claims or affect it in any way.

**Connector Drawings**



**Wiring Diagrams**

