

Basic features

| | |
|---------------------|--------------------------------|
| Approval/Conformity | CE UKCA cULus WEEE |
| Basic standard | IEC 60947-5-2 IEC 60947-5-7 |

Display/Operation

| | |
|--------------------|----------------------|
| Function indicator | Adjustment indicator |
| Power indicator | no |

Electrical connection

| | |
|-----------------------------------|-----------------------------------|
| Cable diameter D | 4.60 mm |
| Cable length L | 0.2 m |
| Connection | M12x1-Male, 4-pin, A-coded |
| Connection type | Cable with connector, 0.20 m, PUR |
| Polarity reversal protected | yes |
| Protection against device mix-ups | yes |
| Short-circuit protection | yes |

Electrical data

| | |
|-------------------------------|-------------|
| Limit frequency -3 dB | 1000 Hz |
| Load resistance RL max. | 500 Ohm |
| No-load current Io max. at Ue | 15 mA |
| Operating voltage Ub | 16...30 VDC |
| Protection class | II |
| Rated insulation voltage Ui | 250 V AC |
| Rated operating voltage Ue DC | 24 V |
| Ripple max. (% of Ue) | 15 % |
| Slope I | 4.85 mA/mm |

Environmental conditions

| | |
|-------------------------|---------------------------------|
| Ambient temperature | -40...80 °C |
| Contamination scale | 3 |
| EN 60068-2-27, Shock | Half-sinus, 30 gn, 11 ms |
| EN 60068-2-6, Vibration | 55 Hz, amplitude 1 mm, 3x30 min |
| IP rating | IP68 |

Functional safety

| | |
|--------------|-------|
| MTTF (40 °C) | 533 a |
|--------------|-------|

Interface

| | |
|---------------------------|---------------------------|
| Analog output | Analog, current 4...20 mA |
| Output characteristic | falling on approach |
| Output current at SI max. | 20 mA |
| Output current at SI min. | 4 mA |
| Output current at Se | 12 mA |

Inductive Sensors
BAW M12MN-ICC35C-BP00,2-GS04
Order Code: BAW004R



Material

| | |
|--------------------------|---------------------------|
| Housing material | Brass, Nickel-free coated |
| Material jacket | PUR |
| Material sensing surface | PBT |

Range/Distance

| | |
|---------------------------------------|--------------|
| Linearity range SI | 0.2...3.5 mm |
| Measuring range | 0.2...3.5 mm |
| Non-linearity max. | ±53 µm |
| Repeat accuracy per BWN | ±7 µm |
| Temperature drift max. from end value | ±5.0 % |

Mechanical data

| | |
|-------------------|--------------------|
| Dimension | Ø 12 x 63 mm |
| Installation | for flush mounting |
| Size | M12x1 |
| Tightening torque | 10 Nm |

Remarks


We recommend to connect the teach line to the negative lead (L-) when not in use.
 Values referenced to axial approach of St 37 target. For other materials correction factors are applied.
 At temperatures below -25°C the cable must be fixed in place.
 The working range can be taught using the Teach line or the BAE PD-AW-008-S04 programmer (order code BAE00MP).
 Scattering (e.g. due to manufacturing tolerances) is described by the tolerance T at Se. This can be approximated using the formula: $T = (sl_{max} + sl_{min}) / 20 = \pm xx \text{ mm}$.
 UL-MARKINGS: - For use in NFPA 79 Applications only - Adapters providing field wiring means are available from the manufacturer. Refer to manufacturers information.
 For more information about MTTF and B10d see MTTF / B10d Certificate

Indication of the MTTF- / B10d value does not represent a binding composition and/or life expectancy assurance; these are simply experiential values with no warranty implications. These declared values also do not extend the expiration period for defect claims or affect it in any way.

Connector Drawings

Wiring Diagrams

Technical Drawings



- 1) Standard characteristic curve
- 2) Reduced measuring range
- 3) Minimum width $S_I/3$