

### Basic features

Approval/Conformity	CE WEEE
---------------------	------------

### Electrical connection

Bending radius min., fixed cable	5 x D
Bending radius min., flexible cable	10 x D
Cable	PUR black, 10 m, drag chain compatible
Cable diameter D	4.60 mm ±0.20 mm
Cable, bending cycles min.	2 mil.
Conductor cross-section	0.50 mm <sup>2</sup>
Connection	A, DIN-0°/180°-Valve connector, angled, 4-pin
Connector configuration	right-angle
Number of conductors	3
Number of pins	4
System	Molded

### Electrical data

Operating voltage U <sub>b</sub>	230 VDC / 230 VAC
Rated current (40 °C)	6.0 A

### Environmental conditions

Cable temperature, drag chain	-25...60 °C
Cable temperature, fixed routing	-50...80 °C
Cable temperature, flexible routing	-25...80 °C
IP rating	IP67

### Material

Cable jacket, material	PUR
Material contact carrier	PA 6.6
Material contacts	Brass
Material grip	TPU
Material locking screw	Steel

Single-Ended Cordsets  
**BCC VA04-0000-10-054-PX0350-100**  
Order Code: **BCC04W8**



**Mechanical data**


Acceleration max., drag chain	5 m/s <sup>2</sup>
Cable jacket, color	black
Cable length L	10.00 m
Cable properties	drag chain compatible

Horizontal travel permitted, drag chain	5 m
Tightening torque pigtail	0.5 Nm
Traverse speed max., drag chain	200 m/min
Vertical travel permitted, drag chain	2 m

**Remarks**

Cable construction acc. to UL-AWM Style 20549  
Halogen-free acc. to EN 50267-2-1  
Silicone-free  
Flame resistance per IEC 60332-2-2  
\* style A per EN 175301-803  
Enclosure rating per IEC 60529, only in screwed state with the associated mating piece.

**Connector Drawings**



PIN 1: brown  
PIN 2: blue  
PIN PE: green/yellow

**Wiring Diagrams**

