



1) Sensing surface



### Basic features

<b>Antenna type</b>	round
<b>Approval/Conformity</b>	CE UKCA cULus WEEE
<b>EN 55011</b>	Size 1, Cl. A
<b>Principle of operation</b>	Data carrier

### Electrical data

<b>Memory organization</b>	32 × 8 bits
<b>Programming cycles</b>	up to 30 °C: 1,000,000 up to 70 °C: 500,000
<b>Programming time</b>	for 1x8 bits: 0.3s for 32x8 bits: 0.6s
<b>Read cycles</b>	Unlimited
<b>Read time</b>	for 32x8 bits: 0.19 s

### Environmental conditions

<b>Ambient temperature</b>	-30...70 °C
<b>Continuous shock load</b>	yes
<b>EN 60068-2-27, Shock</b>	yes
<b>EN 60068-2-32 Free fall</b>	yes
<b>EN 60068-2-6, Vibration</b>	yes
<b>IP rating</b>	IP68
<b>Storage temperature</b>	-30...85 °C
<b>Storage temperature temporary</b>	120 °C 1x700 h

### Functional Characteristics

<b>Memory type</b>	EEPROM
<b>User data, read/write</b>	1023 Byte

### Material

<b>Housing material</b>	Epoxy-resin/fiberglass
-------------------------	------------------------

### Mechanical data

<b>Application weight</b>	1.80 g
<b>Dimension</b>	Ø 12 x 8 mm
<b>Installation</b>	metal-free (clear zone) on metal flush in metal

LF (70/455 kHz)  
**BIS C-103-05/A**  
**Order Code: BIS0004**

**BALLUFF**

#### Remarks

---

Only together with converter BIS C-901 or BIS C-6xx and the appropriate read/write head.  
Values are under rated conditions unless otherwise specified.  
For installation requirements see corresponding read/write head.  
Time specification includes data check.  
IP68 tested according to BWN Pr 36  
On the last page only 31x8 bits are usable.  
For installation in hole Ø12 H11 (glue)