



1) Sensing surface, 2) Clear zone



### Basic features

Antenna type	round
Approval/Conformity	CE UKCA cULus WEEE
EN 55022	Size 1, Cl. B
Principle of operation	Read/write head

### Electrical connection

Connection	M12x1-Male
------------	------------

### Environmental conditions

Ambient temperature	0...70 °C
Continuous shock load	yes
EN 60068-2-27, Shock	yes
EN 60068-2-32 Free fall	yes
EN 60068-2-6, Vibration	yes
IP rating	IP67
Storage temperature	-20...85 °C

### Functional safety

MTTF (40 °C)	15080 a
--------------	---------

### Material

Housing material	1.4305 stainless steel, 1.4305 stainless steel
------------------	--

### Mechanical data

Application weight	90.00 g
Dimension	Ø 30 x 70.5 mm
Installation	metal-free (clear zone)
Size	M30x1.5

LF (70/455 kHz)  
**BIS C-323/05-S4**  
**Order Code: BIS007K**

**BALLUFF**

## Remarks

---

Only together with converter BIS C-901 or BIS C-6xx

Specified relative speed refers to reading/writing the first 4 bytes from the first page.

For basic equipment order cable also, e.g.: BIS C-505-PU1-05 BIS C-505-PU-05 BIS C-506-PU1-05 BIS C-506-PU-05 BIS C-517-PVC-05 BIS C-518-PVC-05

Values are under rated conditions unless otherwise specified.

Time specification includes data check.

For installation in metal: Observe clear zone.

Use included nuts for installation.

For more information about MTTF and B10d see MTTF / B10d Certificate

Indication of the MTTF- / B10d value does not represent a binding composition and/or life expectancy assurance; these are simply experiential values with no warranty implications. These declared values also do not extend the expiration period for defect claims or affect it in any way.

## Help Views

**BIS C-323-\_\_**

	BIS C-104-_/A bündig / flush	BIS C-104-_/A nicht bündig / non-flush	BIS C-108-_/L nicht bündig / non-flush	BIS C-108-_/L-SA2 nicht bündig / non-flush	BIS C-117-05/A bündig / flush	BIS C-117-05/L nicht bündig / non-flush	BIS C-128-_/L bündig / flush	BIS C-128-_/L nicht bündig / non-flush	BIS C-130-05/L-SA1 bündig / flush	BIS C-130-05/L-SA6 nicht bündig / non-flush	BIS C-133-_/L nicht bündig / non-flush	BIS C-134-_/L nicht bündig / non-flush
passende Datenträger Appropriate data carriers												
<b>statischer Betrieb</b>												
<b>Static mode</b>												
Schreibabstand in mm Write distance in mm	1-11	0-12	0-12	0-11	1-12	0-13	0-8	0-13	0-8	0-7	0-10	0-10
Leseabstand in mm Read distance in mm	1-11	0-12	0-12	0-11	1-12	0-13	0-8	0-13	0-8	0-7	0-10	0-10
Versatz in mm bei Abstand von												
0,7												
1	±7,5	±7,5	±10	±10	±7,5	±11	±8	±10	±6,5	±5,5	±10	±9
2												
3	±7	±7	±9	±9	±7,5	±10	±7	±10	±6	±5	±9	±8
4												
5	±7	±7	±9	±8,5	±7	±10	±6,5	±9	±5,5	±4	±9	±7
6												
7	±7	±7	±8,5	±7,5	±6,5	±9,5	±5,5	±9			±7	±4
10												
15												
20												
35												
42												
60												

