



1) Sensing surface, 2) Data carrier



**Basic features**

Antenna type	round
Approval/Conformity	CE UKCA WEEE
EN 55022	Size 1, Cl. B
Principle of operation	Data carrier

**Electrical data**

Data retention time/years	≥ 10 at 55 °C
Memory organization	250 × 8 bits
Programming cycles	≥ 10.000.000.000
Programming time	for 16 bytes: 0.060s
Read cycles	Unlimited
Read time	for 16 bytes: 0.03 s User ID for 8 bytes: 0.02 s

**Environmental conditions**

Ambient temperature	-25...70 °C
Continuous shock load	yes
EN 60068-2-27, Shock	yes
EN 60068-2-32 Free fall	yes
EN 60068-2-6, Vibration	yes
IP rating	IP67
Storage temperature	-25...85 °C

**Functional Characteristics**

Memory type	FRAM
Supported data carrier types	DIN ISO 15693
UID serial number, read-only	8 Byte
User data, read/write	2000 Byte

**Material**

Housing material	PA 12 Cast aluminum
------------------	------------------------

HF (13.56 MHz)  
**BIS M-127-02/A**  
**Order Code: BIS0176**

**BALLUFF**

**Mechanical data**

**Installation**

**Application weight** 180 g  
**Dimension** 93 x 43.3 x 57.2 mm

metal-free (clear zone)  
on metal  
flush in metal

**Remarks**

Time specification includes data check.  
For installation requirements see corresponding read/write head.  
Only when used together with the appropriate read/write head.  
Values are under rated conditions unless otherwise specified.  
Impact loading not permitted.