



## Basic features

|                     |                         |
|---------------------|-------------------------|
| Approval/Conformity | cULus<br>Ecolab<br>WEEE |
|---------------------|-------------------------|

## Electrical connection

|                                     |                                      |
|-------------------------------------|--------------------------------------|
| Bending radius min., fixed cable    | 5 x D                                |
| Bending radius min., flexible cable | 10 x D                               |
| Cable                               | PVC gray, 5 m, drag chain compatible |
| Cable diameter D                    | 4.80 mm ±0.15 mm                     |
| Cable, bending cycles min.          | 2 mil.                               |
| Conductor cross-section             | 0.34 mm <sup>2</sup>                 |
| Connection                          | M12x1-Female, angled, 5-pin, A-coded |
| Connector configuration             | right-angle                          |
| Number of conductors                | 4                                    |
| Number of pins                      | 5                                    |
| System                              | Molded                               |

## Electrical data

|                         |                   |
|-------------------------|-------------------|
| Operating voltage $U_b$ | 250 VDC / 250 VAC |
| Rated current (40 °C)   | 4.0 A             |

## Environmental conditions

|   |                   |
|---|-------------------|
| Cable temperature UL max., fixed routing    | 80 °C             |
| Cable temperature UL max., flexible routing | 80 °C             |
| Cable temperature, drag chain               | -5...60 °C        |
| Cable temperature, fixed routing            | -40...105 °C      |
| Cable temperature, flexible routing         | -5...105 °C       |
| IP rating                                   | IP67, IP68, IP69K |

## Interface

|                  |               |
|------------------|---------------|
| Switching output | Complementary |
|------------------|---------------|

## Material

|                          |                        |
|--------------------------|------------------------|
| Cable jacket, material   | PVC                    |
| Material contact carrier | PUR                    |
| Material contacts        | Bronze                 |
| Material cover nut       | 1.4404 stainless steel |
| Material grip            | PUR                    |

## Mechanical data

|   |                       |
|---|-----------------------|
| Acceleration max., drag chain           | 5 m/s <sup>2</sup>    |
| Cable jacket, color                     | gray                  |
| Cable length L                          | 5.00 m                |
| Cable properties                        | drag chain compatible |
| Horizontal travel permitted, drag chain | 5 m                   |
| Tightening torque pigtail               | 0.6 Nm                |
| Traverse speed max., drag chain         | 200 m/min             |
| Vertical travel permitted, drag chain   | 2 m                   |

## Remarks


Cable construction acc. to UL-AWM Style 2517

Silicone-free

Flame-retarding acc. to IEC 60332-2

Enclosure rating per IEC 60529 or 20653, only in screwed state with the associated mating piece.

## Connector Drawings



PIN 1: brown

PIN 2: white

PIN 3: blue

PIN 4: black

## Wiring Diagrams

