



### Basic features

Approval/Conformity	cULus CE UKCA WEEE
Basic standard	IEC 60947-5-2
Trademark	Global

### Display/Operation

Function indicator	yes
Power indicator	no

### Electrical connection

Connection	M12x1-Male, 4-pin, A-coded
Polarity reversal protected	yes
Protection against device mix-ups	yes
Short-circuit protection	yes

### Electrical data

Load capacitance max. at Ue	0.5 $\mu$ F
Min. operating current Im	0 mA
No-load current Io max., damped	10 mA
No-load current Io max., undamped	3 mA
Operating voltage Ub	10...30 VDC
Output resistance Ra	33.0 kOhm + D
Rated insulation voltage Ui	250 V AC
Rated operating current Ie	200 mA
Rated operating voltage Ue DC	24 V
Rated short circuit current	100 A
Ready delay tv max.	20 ms
Residual current Ir max.	10 $\mu$ A
Ripple max. (% of Ue)	15 %
Switching frequency	300 Hz
Utilization category	DC -13
Voltage drop static max.	2.5 V

### Environmental conditions

Ambient temperature	-25...70 °C
Contamination scale	3
EN 60068-2-27, Shock	Half-sinus, 30 gn, 11 ms
EN 60068-2-6, Vibration	55 Hz, amplitude 1 mm, 3x30 min
IP rating	IP67

### Functional safety

MTTF (40 °C)	640 a
--------------	-------

Inductive Sensors  
**BES M30MM-PSC30F-S04G**  
**Order Code: BES03RE**



**Interface**

Switching output PNP normally open (NO)

**Material**

Housing material Brass, Nickel-free coated  
 Material sensing surface PBT

**Mechanical data**

Dimension Ø 30 x 83 mm  
 Installation non-flush  
 Size M30x1.5  
 Tightening torque 70 Nm

**Range/Distance**

Assured operating distance Sa 24 mm  
 Hysteresis H max. (% of Sr) 20.0 %  
 Rated operating distance Sn 30 mm  
 Real switching distance sr 30 mm  
 Repeat accuracy max. (% of Sr) 5.0 %  
 Switching distance marking ■■  
 Temperature drift max. (% of Sr) 10 %  
 Tolerance Sr ±10 %

**Remarks**

The sensor is functional again after the overload has been eliminated.  
 Not for flush mounting: See installation instructions for inductive sensors with extended range 939229.  
 For more information about MTTf and B10d see MTTf / B10d Certificate

Indication of the MTTf- / B10d value does not represent a binding composition and/or life expectancy assurance; these are simply experiential values with no warranty implications. These declared values also do not extend the expiration period for defect claims or affect it in any way.

**Connector Drawings**



**Wiring Diagrams**

