

1) Sensing surface, 2) see remarks, 3) see remarks, 4) see remarks



Basic features

Application	Pneumatic cylinder with T-slot. For dimensions, see sketch in product view.
Approval/Conformity	CE UKCA cULus WEEE
Basic standard	IEC 60947-5-2
Principle of operation	Magnetic field sensor
Scope of delivery	Cable clip for T-slot
Trademark	Global

Display/Operation

Function indicator	yes
---------------------------	-----

Electrical connection

Cable	PUR, 0.3 m
Cable diameter D	2.50 mm
Connection	M8x1-Male, 3-pin
Polarity reversal protected	no
Protection against device mix-ups	no
Short-circuit protection	yes

Electrical data

Assured switching field strength H_a	2 kA/m
Hysteresis H max. (% of H_n)	45 %
Load capacitance max. at U_e	1 μ F
No-load current I_o max., undamped	6 mA
Operating voltage U_b	10...30 VDC
Output resistance R_a	Open drain
Rated insulation voltage U_i	75 V DC
Rated operating current I_e	200 mA
Rated operating voltage U_e DC	24 V
Rated short circuit current	100 A
Rated switch field strength H_n	1.2 kA/m
Residual current I_r max.	80 μ A
Ripple max. (% of U_e)	15 %
Switching frequency	3000 Hz
Turn-off delay t_{off} max.	0.1 ms
Turn-on delay t_{on} max.	0.1 ms
Utilization category	DC -13
Voltage drop static max.	2.5 V

Environmental conditions

Ambient temperature	-25...85 °C
Contamination scale	3
EN 60068-2-27, Shock	Half-sinus, 30 g_n , 11 ms
EN 60068-2-6, Vibration	55 Hz, amplitude 1 mm, 3x30 min
ESD	3A(8KV)
Emission	Group 1, Class B
IP rating	IP67

Magnetic Sensors
BMF 235K-PO-C-2A-SA2-S49-00,3
Order Code: **BMF00C6**

BALLUFF

Functional safety

MTTF (40 °C) 355 a

Interface

Switching output PNP normally closed (NC)

Material

Housing material PA 12
Material jacket PUR
Material sensing surface PU

Mechanical data

Dimension 23.5 x 5 x 5.5 mm
Mounting part can be installed in T-slot from above
Tightening torque 0.4 Nm

Range/Distance

Temp. drift max. (% of Hn) 0.3 %

Remarks

2) Application area: pneumatic cylinder with t-slot. For dimensions, see sketch in product view.

4) Allen wrench 2.0 mm: max. tightening torque 0.4 Nm. Screw driver 4x0.8 mm: max. tightening torque 1 Nm

Effective operating current I_e with thermally coupled installation in metal.

Damping magnet axially magnetized

UL-MARKINGS: - For use in NFPA 79 Applications only - Adapters providing field wiring means are available from the manufacturer. Refer to manufacturers information.


For more information about MTTF and B10d see MTTF / B10d Certificate

Indication of the MTTF- / B10d value does not represent a binding composition and/or life expectancy assurance; these are simply experiential values with no warranty implications. These declared values also do not extend the expiration period for defect claims or affect it in any way.

Connector Drawings



Wiring Diagrams



Help Views

