



1) Sensing surface



Basic features

Approval/Conformity	CE UKCA cULus WEEE
Basic standard	IEC 60947-5-2

Display/Operation

Function indicator	yes
Power indicator	no

Electrical connection

Cable diameter D	3.00 mm
Cable length L	2 m
Conductor cross-section	0.14 mm ²
Connection type	Cable, 2.00 m, PUR
Number of conductors	3
Polarity reversal protected	yes
Protection against device mix-ups	yes
Short-circuit protection	yes

Electrical data

Load capacitance max. at Ue	0.5 µF
Min. operating current I_m	0 mA
No-load current I_o max., damped	10 mA
No-load current I_o max., undamped	8 mA
Operating voltage U_b	10...30 VDC
Output resistance R_a	Open collector
Rated insulation voltage U_i	75 V DC
Rated operating current I_e	100 mA
Rated operating voltage U_e DC	24 V
Rated short circuit current	100 A
Ready delay t_v max.	20 ms
Residual current I_r max.	10 µA
Ripple max. (% of U_e)	10 %
Switching frequency	3000 Hz
Utilization category	DC -13
Voltage drop static max.	2.5 V

Environmental conditions

Ambient temperature	-25...70 °C
Contamination scale	3
EN 60068-2-27, Shock	Half-sinus, 30 g _n , 11 ms
EN 60068-2-6, Vibration	55 Hz, amplitude 1 mm, 3x30 min
IP rating	IP67

Functional safety

MTTF (40 °C)	735 a
---------------------	-------

Inductive Sensors
BES M05ED-PSC50F-EP02
Order Code: **BES013E**

BALLUFF

Interface

Switching output PNP normally open (NO)

Material

Housing material Stainless steel
Material jacket PUR
Material sensing surface PET-C

Mechanical data

Dimension Ø 5 x 35 mm
Installation non-flush
Size M5x0.5
Tightening torque 1 Nm

Range/Distance

Assured operating distance Sa 4.05 mm
Hysteresis H max. (% of Sr) 20.0 %
Rated operating distance Sn 5 mm
Real switching distance sr 5 mm
Repeat accuracy max. (% of Sr) 10.0 %
Switching distance marking ■■■
Temperature drift max. (% of Sr) 10 %
Tolerance Sr ±10 %

Remarks

Cannot be flush mounted: see installation instructions for inductive sensors with extended switching distance 939224. Avoid pressure and contact in the area of the clear zone cap.

The sensor is functional again after the overload has been eliminated.

EMC: For operating conditions with noise sources

External protection circuit is required. Document 825345.

When using an AC bridge, an electrolytic capacitor $\geq 10\mu\text{F}/40\text{V}$ parallel to Vs is recommended.

For more information about MTTF and B10d see MTTF / B10d Certificate

Indication of the MTTF- / B10d value does not represent a binding composition and/or life expectancy assurance; these are simply experiential values with no warranty implications. These declared values also do not extend the expiration period for defect claims or affect it in any way.

Wiring Diagrams

