



## Basic features

Approval/Conformity	cULus CE UKCA WEEE
Basic standard	IEC 60947-5-2

## Display/Operation

Function indicator	yes
Power indicator	no

## Electrical connection

Cable diameter D	3.00 mm
Cable length L	5 m
Conductor cross-section	0.14 mm <sup>2</sup>
Connection type	Cable, 5.00 m, PUR
Number of conductors	3
Polarity reversal protected	yes
Protection against device mix-ups	yes
Short-circuit protection	yes

## Electrical data

Load capacitance max. at U <sub>e</sub>	0.2 µF
Min. operating current I <sub>m</sub>	1 mA
No-load current I <sub>o</sub> max., damped	3 mA
No-load current I <sub>o</sub> max., undamped	10 mA
Operating voltage U <sub>b</sub>	10...30 VDC
Output resistance R <sub>a</sub>	Open collector
Rated insulation voltage U <sub>i</sub>	75 V DC
Rated operating current I <sub>e</sub>	100 mA
Rated operating voltage U <sub>e</sub> DC	24 V
Rated short circuit current	100 A
Ready delay t <sub>v</sub> max.	15 ms
Residual current I <sub>r</sub> max.	10 µA
Ripple max. (% of U <sub>e</sub> )	10 %
Switching frequency	3000 Hz
Utilization category	DC -13
Voltage drop static max.	2.5 V

## Environmental conditions

Ambient temperature	-25...70 °C
Contamination scale	3
EN 60068-2-27, Shock	Half-sinus, 30 g <sub>n</sub> , 11 ms
EN 60068-2-6, Vibration	55 Hz, amplitude 1 mm, 3x30 min
IP rating	IP67

## Functional safety

MTTF (40 °C)	830 a
--------------	-------

## Interface

Switching output	PNP normally closed (NC)
------------------	--------------------------

Inductive Sensors  
**BES 516-3042-I02-C-PU-05**  
Order Code: BES01A2

# BALLUFF

## Material

Housing material	Aluminium, Anodized
Material jacket	PUR
Material sensing surface	PBT

## Mechanical data

Dimension	25 x 5 x 5 mm
Installation	for flush mounting
Size	5x5

## Range/Distance

Assured operating distance Sa	0.65 mm
Hysteresis H max. (% of Sr)	15.0 %
Rated operating distance Sn	0.8 mm
Real switching distance sr	0.8 mm
Repeat accuracy max. (% of Sr)	5.0 %
Temperature drift max. (% of Sr)	20 %
Tolerance Sr	±10 %

## Remarks

ESD requirements met if housing is grounded.  
The sensor is functional again after the overload has been eliminated.  
For more information about MTTF and B10d see MTTF / B10d Certificate

Indication of the MTTF- / B10d value does not represent a binding composition and/or life expectancy assurance; these are simply experiential values with no warranty implications. These declared values also do not extend the expiration period for defect claims or affect it in any way.

## Wiring Diagrams

