

1) Optical axis receiver, 2) Optical axis emitter, 3) Operating voltage, 4) Light reception/limit area, 5) Sn



Basic features

Approval/Conformity	CE UKCA cULus WEEE
Basic standard	IEC 60947-5-2
Principle of operation	Photoelectric sensor
Series	12M
Style	Cylinder Straight optics

Electrical data

Load capacitance max. at Ue	0.2 µF
Operating voltage U_b	10...30 VDC
Rated insulation voltage U_i	75 V DC
Rated operating current I_e	100 mA
Rated operating voltage U_e DC	24 V
Ripple max. (% of U_e)	15 %
Switching frequency	1000 Hz
Turn-off delay t_{off} max.	0.5 ms
Turn-on delay t_{on} max.	0.5 ms
Utilization category	DC -13
Voltage drop U_d max. at I_e	1.5 V

Display/Operation

Adjuster	Potentiometer 270°
Display	LED green: Power Limit range - LED yellow, flashing LED yellow: Light received
Setting	Rated switching distance (Sn)

Environmental conditions

Ambient temperature	-5...55 °C
Contamination scale	3
EN 60068-2-27, Shock	Half-sinus, 30 g _n , 11 ms, 3x6
EN 60068-2-6, Vibration	10...55 Hz, amplitude 1 mm, 3x30 min
IP rating	IP67

Electrical connection

Cable diameter D	4.70 mm
Cable length L	2 m
Conductor cross-section	0.34 mm ²
Connection	Cable, 2.00 m, PVC
Number of conductors	3
Polarity reversal protected	yes
Protection against device mix-ups	yes
Short-circuit protection	yes

Functional safety

MTTF (40 °C)	1428 a
---------------------	--------

Interface

Switching output	PNP normally open (NO)
-------------------------	------------------------

Material

Housing material	Brass, nickel-plated
Material jacket	PVC
Material sensing surface	PMMA
Surface protection	nickel-plated

Mechanical data

Dimension	Ø 12 x 60 mm
Mounting part	Nut M12x1
Tightening torque max.	7 Nm 15 Nm

Optical features

Ambient light max.	10000 Lux
Beam characteristic	Divergent
LED group per IEC 62471	Exempt Group
Light spot size	45 x 45 mm at 400 mm
Light type	Infrared
Principle of optical operation	Diffuse sensor, energetic
Switching function, optical	Light-on
Wave length	850 nm

Range/Distance


Hysteresis H max. (% of Sr)	10.0 %
Range	1...400 mm
Rated operating distance S _n	400 mm Adjustable
Temperature drift max. (% of Sr)	10 %

Remarks

Order accessories separately.
 For additional information, refer to user's guide.
 Reference object (target): gray card, 200 x 200, 90 % remission, axial approach.
 The sensor is functional again after the overload has been eliminated.
 For more information about MTTF and B10d see MTTF / B10d Certificate

Indication of the MTTF- / B10d value does not represent a binding composition and/or life expectancy assurance; these are simply experiential values with no warranty implications. These declared values also do not extend the expiration period for defect claims or affect it in any way.

Wiring Diagrams



Opto Symbols

