



1) Sensing surface



Basic features

| | |
|----------------------------|-----------------------------|
| Approval/Conformity | CE UKCA cULus WEEE |
| Basic standard | IEC 60947-5-2 |

Display/Operation

| | |
|---------------------------|-----|
| Function indicator | yes |
| Power indicator | no |

Electrical connection

| | |
|--|----------------------|
| Cable diameter D | 3.00 mm |
| Cable length L | 3 m |
| Conductor cross-section | 0.14 mm ² |
| Connection type | Cable, 3.00 m, PUR |
| Number of conductors | 3 |
| Polarity reversal protected | yes |
| Protection against device mix-ups | yes |
| Short-circuit protection | yes |

Electrical data

| | |
|---|---------------|
| Load capacitance max. at Ue | 0.5 µF |
| Min. operating current I_m | 0 mA |
| No-load current I_o max., damped | 4 mA |
| No-load current I_o max., undamped | 12 mA |
| Operating voltage U_b | 10...30 VDC |
| Output resistance R_a | 33.0 kOhm + D |
| Rated insulation voltage U_i | 75 V DC |
| Rated operating current I_e | 200 mA |
| Rated operating voltage U_e DC | 24 V |
| Rated short circuit current | 100 A |
| Ready delay t_v max. | 10 ms |
| Residual current I_r max. | 80 µA |
| Ripple max. (% of U_e) | 15 % |
| Switching frequency | 3000 Hz |
| Utilization category | DC -13 |
| Voltage drop static max. | 2.5 V |

Environmental conditions

| | |
|--------------------------------|---------------------------------------|
| Ambient temperature | -25...70 °C |
| Contamination scale | 3 |
| EN 60068-2-27, Shock | Half-sinus, 30 g _n , 11 ms |
| EN 60068-2-6, Vibration | 55 Hz, amplitude 1 mm, 3x30 min |
| IP rating | IP67 |

Functional safety

| | |
|---------------------|-------|
| MTTF (40 °C) | 830 a |
|---------------------|-------|

Inductive Sensors
BES Q08ZE-POC20B-BP03
Order Code: BES01UF

BALLUFF

Interface

Switching output PNP normally closed (NC)

Material

Housing material Zinc, Die casting
Material jacket PUR
Material sensing surface PBT

Mechanical data

Dimension 40 x 8 x 8 mm
Installation for flush mounting
Size 8x8

Range/Distance

Assured operating distance Sa 1.6 mm
Hysteresis H max. (% of Sr) 15.0 %
Rated operating distance Sn 2 mm
Real switching distance sr 2 mm
Repeat accuracy max. (% of Sr) 5.0 %
Switching distance marking ■■
Temperature drift max. (% of Sr) 10 %
Tolerance Sr ±10 %

Remarks

The sensor is functional again after the overload has been eliminated.
For more information about MTTF and B10d see MTTF / B10d Certificate

Indication of the MTTF- / B10d value does not represent a binding composition and/or life expectancy assurance; these are simply experiential values with no warranty implications. These declared values also do not extend the expiration period for defect claims or affect it in any way.

Wiring Diagrams

